

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0190750007**
Status: **Active**
Overview: Solderless Terminals
Description: InsulKrimp Steel Star Ring Tongue Terminal for 18-22 AWG Wire, Stud Size 6 (M3.5)

Documents:

3D Model	Product Specification PS-19902-011-001 (PDF)
Drawing (PDF)	Product Specification PS-19902-013-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19902-009-001 (PDF)	

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Ring and Spade Terminals
Series	<u>19075</u>
Crimp Quality Equipment	Yes
Overview	<u>Solderless Terminals</u>
Product Name	InsulKrimp
Type	Ring
UPC	800753079489

Physical

Barrel Type	Closed
Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin
Net Weight	0.610/g
Packaging Type	Bag
Stud Size	6 (M3.5)
Wire Insulation Diameter	3.68mm
Wire Size AWG	18, 20, 22

Material Info

Engineering Number	SRA-S-229-06X
--------------------	---------------

Reference - Drawing Numbers

Product Specification	PS-19902-009-001, PS-19902-011-001, PS-19902-013-001
-----------------------	---



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
reaction mass of
2-ethylhexyl 10-
ethyl-4,4-dioct
Methylhexahydrophthalic
anhydride
Nonadecafluorodecanoic
acid (PFDA) and its
sodiu
Aluminosilicate
Refractory Ceramic
Fibres
Boric acid
diisohexyl phthalate
Terphenyl,
hydrogenated
2-(2H-Benzotriazol-2-
yl)-4-(tert-butyl)-6-
(sec-b
2-(2H-Benzotriazol-2-
yl)-4,6-
ditertpentylphenol
Dibutylbis(pentane-2,4-
dionato-O,O')tin
Disodium-octaborate
Dibutyltin-dichloride
1,2-
Benzenedicarboxylic
acid, bis(3-
methylbutyl)
Disodium 3,3'-[[1,1'-
Biphenyl]-4,4'-
Diylbis(Azo)
Octanoic acid,
2,2,3,3,4,4,5,5,6,6,7,7,8,8,8-
pen
Benzo(ghi)perylene

China RoHS

Dipentyl phthalate
Imidazolidine-2-thione
Phenanthrene
Dihexyl-phthalate
4-aminoazobenzene
Silicic acid (H₂Si₂O₅),
barium salt (1:1),
lead-
Cyanamide, lead(2+)
salt (1:1)
Lead titanium
zirconium oxide
Dioxobis(stearato)trilead
Tetralead-trioxide-
sulphate
Pentalead-tetraoxide-
sulphate
pyrochlore, antimony
lead yellow
Cadmium
Lead
Cadmium-sulphide
Cadmium-oxide
Diboron-trioxide
1,2-Dimethoxyethane
1,2-
Benzenedicarboxylic
acid, bis(2-
methoxyethyl
Pentazinc-chromate-
octahydroxide
Potassium
hydroxyoctaoxidizincatedichromate
bis(2-methoxyethyl)
ether
Boric acid, disodium
salt, hydrate
Tris(2-chloroethyl)
phosphate
Lead chromate
molybdate sulfate red
Lead chromate

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[19075 Series](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	640010500

Crimp Head for the 640050500
AT-200 Pneumatic
Hand Tool

This document was generated on 10/11/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19075-0007](#)