

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0022552103](#)
Status: **Active**
Overview: SL™ Modular Connectors
Description: 2.54mm Pitch SL™ Crimp Housing, Dual Row, Version C, Back Ribs, 10 Circuits

Documents:

3D Model	Product Specification TS-70058-001-001 (PDF)
Drawing (PDF)	Product Specification TS-70541-001-001 (PDF)
Product Specification PS-70058-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-70400-001 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	70450
Application	Signal, Wire-to-Board
Comments	Version C
Overview	SL™ Modular Connectors
Product Name	SL™
UPC	800755673852

Physical

Breakaway	No
Circuits (maximum)	10
Color - Resin	Black
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Material - Resin	Polyester
Net Weight	0.960/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Stackable	Yes
Temperature Range - Operating	-40°C to +105°C

Solder Process Data


Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	70450-0103
--------------------	------------

Reference - Drawing Numbers

Product Specification	PS-70058-001, PS-70400-001, TS-70058-001-001, TS-70541-001-001
Sales Drawing	SD-70450-0100-0125



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[70450 Series](#)

Mates With

2.54mm Pitch C-Grid® Header [70229](#) ,
[70280](#) , [70246](#) , [70247](#)

Use With

[70058](#) , [71851](#)