



## GM-5212

Order No.: 23.4380

**Price upon request**

### PRODUCTINFOS

#### Electret gooseneck microphones

- Supercardioid polar pattern
- Excellent sound with a very high speech intelligibility
- Minimum susceptibility to acoustic feedback
- Solid and high-quality workmanship to ensure a long service life
- Gooseneck with integrated 3-pole XLR plug
- Operation via external phantom power or microphone base ST-5030

### TECHNICAL SPECIFICATIONS

#### GM-5212

Type	gooseneck microphone
Transmission method	cable
Polar pattern	supercardioid
System	back electret

**GM-5212**

Audio frequency range	80-18,000 Hz
Nominal impedance	220 $\Omega$ $\pm$ 30%
Sensitivity	16 mV/Pa
Max. sound pressure	125 dB
Power supply	DC 48 V phantom power
Admiss. ambient temp.	0-40 °C
Dimensions	455 mm
Weight	165 g
Connection	XLR, bal.