


No.	1	2	3	4	5	6	7	8	1-8	1-8	
M8	4	4	4	4	4	4	4	4	(+)	(-)	
cable color	white	green	yellow	grey	pink	red	black	violet	brown	blue	
	15-30 V (DC)										
	2A per Signal										
	6A total										



Electrical data:

- Rated voltage: 15-30V DC
- Nominal: 2 A per Contact
- Current: 6 A max total
- Protection level: IP 67
- Temperature range: -25°C...+80°C

PUR, max. 10x0.34 + 2x0.75	10
Type of cable	Dim. a[m]

All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
All rights reserved Department HCS - RO	Created by	Inspected by	Standardisation	Date	State		Doc-Key / ECM-Nr. 100689681/UGD/000/C 500000118447
	MUNTEANV	POPESCU	AVRAM	2017-04-24	Final Release		
HARTING Customised Solutions D-32427 Minden		Title		Number		Rev.	Page
		har-SAB M8/8/3p PAC		090700120100		C	1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[090700120100](#)