





a; 1; RL

H G F E D C B A



Material :
 POLYAMIDE PA 6 / UL94-V0 / COLOUR : GREY
 I3F2 in accordance with NF F 16101
 and NF F 16102 standard
Performance characteristics :
 Operating temperature : -40°C to 105°C
 Insulation resistance : 5000M Ohm Min.
 Test potential : 2000 VAC
 Durability : 500 Cycles



NOTA :
 1- Connector accepts TRIMTRIO formed, machined and subminiature coaxial pin and socket contacts.
 2- Raised contact marking on both : mating and wiring face.
 3- Discrimination with pins is guaranteed without loss of contact positions.
 If discrimination pins are needed : order SMSPE3 per BS.C.201424.003.
 5- For the configuration of all sizes see drawinf : BS.C.201424.010 same as SMS--RDH1
 6- For intermateability with other parts see drawing : BS.C.201424.008

Catalog Number	Quantity of Contact cavities	Quantity of discrimination cavities	Dimensions in mm				
			B±0.5	C±0.3	D±0.3	E±0.3	F
SMS2RD3	2	0	9.9	8.4	11.1	14.1	14.9
SMS3RD3	3	0	9.9	8.4	16.2	18.6	19.4
SMS4RD3	4	0	9.9	8.4	21.2	23.7	24.5
SMS6RD3	6	2	15	13.4	16.2	18.6	19.4
SMS9RD3	9	4	20	18.5	16.2	18.6	19.4
SMS12RD3	12	6	25.1	23.6	16.2	18.6	19.4
SMS15RD3	15	8	30.2	28.7	16.2	18.6	19.4
SMS18RD3	18	10	35.3	33.8	16.2	18.6	19.4
SMS24RD3	24	15	35.3	33.8	21.2	23.7	24.5
SMS36RD3	36	24	25.1	23.6	46.6	49.1	49.9

P/N : SMSXXRD3

a	29/04/14	Creation of PRO-E drawing	23524
ISS	DATE	Latest modification - by: --	MOD N°
Designed by: ROUILLARD		Date: 29/04/14	CUSTOMER DRAWING
TITLE		QIKMATE RECEP. WITHOUT MOULDED-ON HOOD AND DISC.CAV	
		SMS CONNECTOR	
Scale	2/1	General linear Tolerances: ± 0.2	NPRDS / PROJECT TRIMTRIO
SOURIAU		WWW.SOURIAU.COM	
This document is the property of SOURIAU			SHEET
It must not be reproduced or communicated without permission			
FORMAT	SOURIAU DRG N°		1 / 1
A3	BSC201424017		

H G F E D C B A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Souriau:](#)

[SMS12RD3](#)