



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBERS	LEGEND [each]	MARKERS PER WAND	MARKERS PER PKG.	STD. PKG. QTY.	STD. CTN. QTY.	WIRE SIZE RANGE
PCA18-A THRU PCA18-Z	'A' THRU 'Z'	30	300	1	10	.185" - .234"
PCA18-A-J	'A'-'J' [1 EA.]	30	300	1	10	.185" - .234"
PCA18-K-T	'K'-'T' [1 EA.]	30	300	1	10	.185" - .234"
PCA18-U-Z	'U'-'Z' [1 EA.] '-' [2 EA.] '+' [2 EA.]	30	300	1	10	.185" - .234"
PCA18-0 THRU PCA18-9	'0' THRU '9'	30	300	1	10	.185" - .234"
PCA18-0-9	'0'-'9' [1 EA.]	30	300	1	10	.185" - .234"
PCA18-MIN	'-'	30	300	1	10	.185" - .234"
PCA18-PLS	'+'	30	300	1	10	.185" - .234"

NOTES:

- COLOR: WHITE WITH BLACK LEGENDS.
- MILLIMETERS ARE IN [],
- TWO SIDES PRINTED.



SYMBOLS ARE LOCATED ON BOTH SIDE OF MARKERS.

5

5

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
5	10/27/15	RVU	SEWH	JHAC	ADD NOTE 3 TO SHOW TWO SIDES PRINTED.	GAECN03228
4	4/22/13	RVU	SEWH	JHAC	CHANGE OLD DRAWING BOARDER TO NEW PANDUIT DRAWING BOARDER.	GAECN02987
3	3/28/11	RVU			ADD '-' 2 EA. AND '+' 2 EA. '0'-'9', 'A'-'J', 'K'-'T' SHOULD BE [1 EA.].	6336
2	8/11/10	RVU			UPDATE ON TABLE, NOTES, & TOLERANCES. CHG. FROM B TO A FORMAT.	6079
1	10/6/06	RVU			ADDED TOLERANCE AND REVISED TABLE.	4881
0	9/12/06	RVU			DRAWING RELEASE.	3732

TITLE		PCA18-* CLIP-ON WIRE MARKER		
ITEM REVISION NAME		CUSTOMER DRAWING		
DATASET FILE NAME		100281DC/06		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				
.x ± .12 [3.05] .xxx ± .025 [.635] .xx ± .062 [1.57] ANGLES ±				
DRAWING NUMBER:		C10396		
DRAWN BY	DATE	CHK	SCALE	SIZE
RVU	10/14/04	JM	NTS	A
SHT 1 OF 1				

D101000DA/15

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PCA18-1](#) [PCA18-2](#) [PCA18-3](#) [PCA18-4](#) [PCA18-5](#) [PCA18-6](#) [PCA18-7](#) [PCA18-8](#) [PCA18-9](#) [PCA18-W](#) [PCA18-M](#)
[PCA18-O](#) [PCA18-X](#) [PCA18-0](#) [PCA18-E](#) [PCA18-K](#) [PCA18-H](#) [PCA18-K-T](#) [PCA18-A](#) [PCA18-T](#) [PCA18-F](#) [PCA18-Z](#)
[PCA18-G](#) [PCA18-V](#) [PCA18-S](#) [PCA18-P](#) [PCA18-B](#) [PCA18-D](#) [PCA18-U](#) [PCA18-U-Z](#) [PCA18-J](#) [PCA18-Y](#) [PCA18-](#)
[C](#) [PCA18-MIN](#) [PCA18-R](#) [PCA18-Q](#) [PCA18-PLS](#) [PCA18-L](#) [PCA18-I](#) [PCA18-0-9](#) [PCA18-A-J](#) [PCA18-N](#)