


# SMD Power Inductor CDR7D43MN




## Description

- Ferrite drum core construction.
- Magnetically shielded.
- L × W × H: 7.6 × 7.6 × 4.5 mm Max.
- Product weight: 0.84g(Ref.)
- Moisture Sensitivity Level: 1
- RoHS compliance.

## Dimension - [mm]



## Land pattern and Schematics - [mm]



## Environmental Data


- Operating temperature range:  $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$  (including coil's self temperature rise)
- Storage temperature range:  $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
- Solder reflow temperature:  $260^{\circ}\text{C}$  peak.

## Packaging

- Carrier tape and reel packaging
- 13.0" diameter reel
- 1000pcs per reel

## Applications

- Ideally used in LCD Driver, DSC/DVC, Notebook PC etc as DC-DC converter inductors.



### Electrical Characteristics

PART NO.	STAMP	INDUCTANCE [WITHIN] ※1	D.C.R. (mΩ) MAX. (Typ.) (at 20°C)	SATURATION CURRENT (A) ※2		TEMPERATURE RISE CURRENT (A) ※3
				(at20°C)	(at105°C)	
CDR7D43MNNP-3R7NC	3R7	3.7μH±25%	18.9(15.1)	6.95	5.60	4.3
CDR7D43MNNP-4R7NC	4R7	4.7μH±25%	21.4(17.1)	6.20	4.85	4.0
CDR7D43MNNP-5R8NC	5R8	5.8μH±25%	24.0(19.1)	5.60	4.20	3.7
CDR7D43MNNP-7R2NC	7R2	7.2μH±25%	33.9(27.2)	4.95	3.90	3.0
CDR7D43MNNP-100NC	100	10μH±25%	48.4(38.7)	4.10	3.25	2.5
CDR7D43MNNP-120NC	120	12μH±25%	56.8(45.4)	3.90	3.05	2.1
CDR7D43MNNP-150NC	150	15μH±25%	80.4(64.3)	3.35	2.75	1.8
CDR7D43MNNP-180NC	180	18μH±25%	93.6(74.9)	3.05	2.40	1.6
CDR7D43MNNP-220NC	220	22μH±25%	106.4(85.1)	2.85	2.20	1.5
CDR7D43MNNP-270NC	270	27μH±25%	143.6(114.9)	2.50	2.00	1.25
CDR7D43MNNP-330NC	330	33μH±25%	160.0(127.7)	2.30	1.75	1.15
CDR7D43MNNP-390NC	390	39μH±25%	175.0(140.0)	2.10	1.65	1.10
CDR7D43MNNP-470NC	470	47μH±25%	247.0(197.6)	1.90	1.45	0.90
CDR7D43MNNP-560NC	560	56μH±25%	266.3(213.0)	1.75	1.35	0.85
CDR7D43MNNP-680NC	680	68μH±25%	363.8(291.1)	1.55	1.25	0.75
CDR7D43MNNP-820NC	820	82μH±25%	401.4(321.1)	1.45	1.15	0.65
CDR7D43MNNP-101NC	101	100μH±25%	455.8(364.6)	1.25	1.05	0.55

※1. Measuring condition: at 100kHz.

※2. Saturation current: The value of D.C. current when the inductance decreases to 65% of it's nominal value.


※3. Temperature rise current: The value of D.C. current when the temperature rise is  $\Delta t=40^{\circ}\text{C}$  ( $T_a=20^{\circ}\text{C}$ ).

# SMD Power Inductor CDR7D43MN



## Saturation Current & Temperature Rise Graph

— L (20°C) — L (105°C) —  $\Delta T$








# SMD Power Inductor CDR7D43MN




## Saturation Current & Temperature Rise Graph

— L (20°C) — L (105°C) —  $\Delta T$




## Solder Reflow Condition

Heat Endurance



Temperature Chart



Please refer to the sales offices on our website - <http://www.sumida.com>

### Hong Kong

Tel. +852-2880-6781  
FAX. +852-2565-9600  
[sales@hk.sumida.com](mailto:sales@hk.sumida.com)

### Saitama(Japan)

Tel. +81-48-691-7300  
FAX. +81-48-691-7340  
[sales@jp.sumida.com](mailto:sales@jp.sumida.com)

### Chicago

Tel. +1-847-545-6700  
FAX. +1-847-545-6720  
[sales@us.sumida.com](mailto:sales@us.sumida.com)

### Shanghai

Tel. +86-21-5836-3299  
FAX. +86-21-5836-3266  
[shanghai.sales@cn.sumida.com](mailto:shanghai.sales@cn.sumida.com)

### Seoul

Tel. +82-2-6237-0777  
FAX. +82-2-6237-0778  
[sales@kr.sumida.com](mailto:sales@kr.sumida.com)

### Obernzell

Tel. +49-8591-937-0  
FAX. +49-8591-937-103  
[contact@eu.sumida.com](mailto:contact@eu.sumida.com)

### Shenzhen

Tel. +86-755-8291-0228  
FAX. +86-755-8291-0338  
[shenzhen.sales@cn.sumida.com](mailto:shenzhen.sales@cn.sumida.com)

### Singapore

Tel. +65-6296-3388  
FAX. +65-6841-4426  
[sales@sg.sumida.com](mailto:sales@sg.sumida.com)

### Neumarkt

Tel. +49-9181-4509-110  
FAX. +49-9181-4509-310  
[infocomp@eu.sumida.com](mailto:infocomp@eu.sumida.com)

### Taipei

Tel. +886-2-8751-2737  
FAX. +886-2-8751-2738  
[sales@tw.sumida.com](mailto:sales@tw.sumida.com)

### San Jose

Tel. +1-408-321-9660  
FAX. +1-408-321-9308  
[sales@us.sumida.com](mailto:sales@us.sumida.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Sumida:

[CDR7D43MNNP-100NC](#) [CDR7D43MNNP-820NC](#) [CDR7D43MNNP-4R7NC](#) [CDR7D43MNNP-101NC](#)  
[CDR7D43MNNP-470NC](#) [CDR7D43MNNP-180NC](#) [CDR7D43MNNP-330NC](#) [CDR7D43MNNP-560NC](#)  
[CDR7D43MNNP-680NC](#) [CDR7D43MNNP-390NC](#) [CDR7D43MNNP-150NC](#) [CDR7D43MNNP-270NC](#)  
[CDR7D43MNNP-7R2NC](#) [CDR7D43MNNP-3R7NC](#) [CDR7D43MNNP-220NC](#) [CDR7D43MNNP-5R8NC](#)  
[CDR7D43MNNP-120NC](#)