



# Self-aligning ball bearings, cylindrical and tapered bore, cylindrical bore, unsealed



Principal dimensions			Basic load ratings		Fatigue load limit $P_u$	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
25	52	15	14,3	4	0,21	28000	18000	0,14	1205 ETN9



### Calculation factors

- $e$  0,28
- $Y_1$  2,2
- $Y_2$  3,5
- $Y_0$  2,5