

Data sheet

Commercial Art.No.: 70.331.0635.0

Bottom BAS GUT GM 6 M20 A0

revos BASIC size 6 closed-bottom base with cable gland M20, left single locking lever

1011011010001010010101101
0100110110010110100101010
101001101100111001010010
101001101100111001010010
101001101100111001010010
1101010011011001011010010
10101010010101101010011

**DIGITALIZATION
IN PROGRESS**

Commercial Art.No.	70.331.0635.0
EAN	4015573616387
Order Unit	1

Certificates / Approvals



Technical data

General

Housing material	Aluminium
Color	Grey
Surface	With powder coating
Degree of protection (IP)	IP54
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

Construction	6
Model	Surface mounting (base)
Locking mechanism	Single locking lever
Cable entry	Sideways
Type of cable	Gland nut
With cable screw gland	Yes
Thread size M	20
Thread size PG	
Hinged lid	No
EMC-version	No
Length	84 mm
Width	52 mm
Height	54.7 mm

Classification

ECLASS 8.1	27440202
ETIM 7.0	EC000437
ETIM 6.0	EC000437

ETIM 5.0	EC000437
ETIM 4.0	EC000437
ETIM 3.0	EC000437