

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638117400](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: PremiumGrade Hand Crimp Tool for KK 3.96mm Terminals, 22-26 AWG

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207129
Comments	Field Repair, See Tooling Specification (PDF) Above. Type: 2C
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	822350924245
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.


Physical

Net Weight 576.034/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents
ATS-6381174HM-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Not Relevant

Not Relevant

Not Contained

Search Parts in this Series

[207129 Series](#)

Use With

Loose Piece Terminals

Application Tooling | **FAQ**

Description	Product #
KK 396 Crimp Terminal 2578, 22-26 AWG, Reel, Brass, 2.540µm Tin (Sn)	8500107
KK 396 Crimp Terminal 2578, 22-26 AWG, Bag, Brass, 2.540µm Tin (Sn)	8500108
KK 396 Crimp Terminal 2578, 22-26 AWG, Reel, Phosphor Bronze, 2.540µm Tin (Sn)	8500133
KK 396 Crimp Terminal 2578, 22-26 AWG, Bag,	8500134

Phosphor Bronze, 2.540µm Tin(Sn) KK Trifurcon Crimp	<u>8520124</u>
Terminal 7258, 22-26 AWG, Reel, Phosphor Bronze Tin(Sn) KK Trifurcon Crimp	<u>8520125</u>
Terminal 7258, 22-26 AWG, Bag, Phosphor Bronze Tin (Sn) KK 396 Crimp	<u>8550105</u>
Terminal 2578, 22-26 AWG, Reel, Brass, 0.38µm Selective Gold (Au) KK 396 Crimp	<u>8550106</u>
Terminal 2578, 22-26 AWG, Bag, Brass, 0.38µm Selective Gold(Au) KK 396 Crimp	<u>8560107</u>
Terminal 2578, 22-26 AWG, Reel, Brass, 0.51µm Select Gold (Au) over Gold Flash KK 396 Crimp	<u>8560108</u>
Terminal 2578, 22-26 AWG, Bag, Brass, 0.51µm Select Gold (Au) over Gold Flash KK Trifurcon Crimp	<u>8560123</u>
Terminal 7258, 22-26 AWG, Reel, Phosphor Bronze Gold (Au) KK Trifurcon Crimp	<u>8560124</u>
Terminal 7258, 22-26 AWG, Bag, Phosphor Bronze Gold(Au) KK 396 Crimp	<u>8580125</u>
Terminal 2578, 22-26 AWG, Reel, Phosphor Bronze, 0.51µm Selective Gold (Au) KK 396 Crimp	<u>8580126</u>
Terminal 2578, 22-26 AWG, Bag, Phosphor Bronze, 0.51µm Selective Gold (Au) KK 396 Crimp	<u>8650116</u>
Terminal 2578, 22-26 AWG, Reel, Phosphor Bronze, 0.38µm Selective Gold (Au) KK 396 Crimp	<u>8650117</u>
Terminal 2578, 22-26 AWG, Bag, Phosphor Bronze,	

0.38µm Selective
Gold (Au)
KK Trifurcon Crimp 8650121
Terminal 7258,
22-26 AWG, Reel,
Phosphor Bronze
Selective Gold (Au)
KK Trifurcon Crimp 8650122
Terminal 7258,
22-26 AWG, Bag,
Phosphor Bronze
Selective Gold (Au)
KK 156 TERMINAL 40011117
CRIMP 22-26 AWG

This document was generated on 06/26/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63811-7400](#)