

Pneum. contact metal OD 3 female



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 000 6453
Specification	Pneum. contact metal OD 3 female
HARTING eCatalogue	https://b2b.harting.com/09140006453

Identification

Category	Contacts
Type of contact	Pneumatic contact
Description of the contact	Without shut-off Straight
Features	The Han® Pneumatic contacts without shut-off are suitable for the use inside a vacuum. (Limit: 100 mbar = 100 hPa ≈ approx 90% vacuum)

Version

Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Limiting temperature	-20 ... +85 °C Tube outer diameter
Operating pressure	≤10 bar
Tube outer diameter	3 mm

Material properties

Material (contacts)	Brass
Material (seal)	NBR
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No



Pushing Performance

Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

Commercial data

Packaging size	10
Net weight	12 g
Country of origin	Germany
European customs tariff number	39269097
eCl@ss	27440204 Contact for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09140006453](#)