

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size	500 kcmil
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric
Wire Strip Length	1-13/16 in.
Stud Size	3/8 in.
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90 ° C
C.S.A Certified Wire Connector	Yes
Panduit Color Code on Barrel	BROWN
Panduit Die Index No. on Barrel	P87 (20)
Alternate Industry Die Index No. () on Barrel	



CERTIFIED



LISTED
Wire Connector



PANDUIT

CORP. TINLEY PARK, ILLINOIS

LCAN500-38-6

Copper Lug - One-Hole, Narrow Tongue, Standard Barrel

REV DATE BY CHK

01 11/08 DRL DRL

DESCRIPTION

ECN

SCALE N/A

DRAWING NO / CAD FILE

LCAN500-38-CUST

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[LCAN500-38-6](#)