

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0193230005](#)
Status: **Active**
Overview: [Metric Ring Terminals](#)
Description: VersaKrimp Metric Ring Terminal for M5 Stud Size (#10), Un-insulated, Bag

Documents:

Drawing (PDF)	3D Model
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL E32244

General

Product Family	Ring and Spade Terminals
Series	19323
Crimp Quality Equipment	Yes
Overview	Metric Ring Terminals
Product Name	VersaKrimp
Type	Ring
UPC	887191289199

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Net Weight	0.889/g
Packaging Type	Bag
Stud Size	M5
Wire Size AWG	N/A
Wire Size mm ²	0.50-1.00

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number AA1-322-M5

Reference - Drawing Numbers

Sales Drawing SD-19323-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19323 Series](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm ² - 0.5mm ²	640030100
Crimp Head for the AT-200 Pneumatic Hand Tool	640070100
ServiceGrade Hand Crimp Tool - Ratchet	640160038

This document was generated on 02/08/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19323-0005](#)