


Specification Sheet

Part Number: 151-01403



The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters.

Bundling Clip w/Oval Fir Tree, 2.28" L, 0.02 - 0.24" Panel Thickness, PA66HIRHSUV, Black, 8000/ctn

Article Number 151-01403

Type BCFTOVAL

Color Black (BK)

Quantity Per carton

Product Description HellermannTyton Bundling Clips are designed to provide simple and easy methods for securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties.

Short Description Bundling Clip w/Oval Fir Tree, 2.28" L, 0.02 - 0.24" Panel Thickness, PA66HIRHSUV, Black, 8000/ctn

Global Part Name BCFTOVAL-PA66HIRHSUV-BK

Length L (Imperial)	2.28
Length L (Metric)	58.0
Fixation Method	Fir Tree for oval holes
Height H (Imperial)	0.60
Height H (Metric)	15.45
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.24
Panel Thickness Min (Metric)	0.51
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.24 x 0.48 " 0.26 x 0.50 " 0.26 x 0.51 " 0.28 x 0.47
Mounting Hole Diameter D (Metric)	7.0 x 12.0 mm 6.2 x 12.2 mm 6.5 x 12.5 mm 6.5 x 13.0 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.51
Mounting Hole Diameter D Max (Metric)	13.0

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	8000
Package Quantity (Metric)	8000
Customs Number	3926909988