





**M12 FEMALE 90° SHIELDED WIREABLE SCREW TERM.**5-pol. max.0,75mm<sup>2</sup> 4-6mm

Female 90°  
M12, 5-pole  
shielded  
Screw terminals  
Sealing range (cable Ø): 4...6 mm

[Link to Product](#)**Illustration**

Female





Product may differ from Image

**Form**

Form 13421

**Technical Data**

Operating voltage	max. 60 V AC/DC
Operating current per contact	max. 4 A
Connection cross section	max. 0.75 mm <sup>2</sup>
Sealing range (cable Ø)	4...6 mm
Protection	IP67 inserted and tightened (EN 60529)
Housing	Brass, nickel plated

**General data**

Temperature range -40...+85 °C

**Commercial data**

country of origin	DE
customs tariff number	85369010
EAN	4048879198783
eClass	27279221

Packaging unit

1