

## High-Speed HDMI Cable with Ethernet (M/M) - 4K, No Signal Booster Needed, CL2 Rated, Black, 50 ft.

MODEL NUMBER: P568-050-HD-CL2



High-speed 4K cable connects audio/video components to an HDTV or monitor in your home theater or digital signage application.

### Features

**4K HDMI Cable Connects Home Theater or Digital Signage Audio/Video Components** This high-speed HDMI cable securely connects HDMI-enabled Chromebooks, MacBooks, tablets, PCs, Blu-ray players, game consoles, Roku/Apple TV boxes or satellite/cable TV receivers to HDTVs, HD monitors, projectors or home theater receivers. It allows you to extend your HDMI signal as far as 50 feet (15.2 meters) from the source without connecting a signal booster or having to use more expensive active optical cable (AOC) or Cat5/6 cable. It also supports Ethernet data speeds up to 18 Gbps, so no separate cable is needed to connect devices online.

**Enjoy the Clarity of 4K HDMI Video with Multi-Channel Audio** This Tripp Lite 4K HDMI cable provides a pure digital connection that supports Ultra HD video resolutions up to 4096 x 2160 (4K x 2K) at 30 Hz for crystal-clear picture and sound.

**Invest in Quality Construction for Reliable Performance** High-quality materials ensure outstanding performance throughout the 24 AWG cable's lifetime. The PVC jacket carries a CL2 rating, making it suitable for in-wall cable installation. Contacts and connectors are gold-plated to resist corrosion. Double shielding reduces line noise (EMI/RFI) that can disrupt signals traveling through the HDMI cord. When used with an Apple digital A/V adapter, the cable supports iPad2 video mirroring for playing games, watching videos or displaying presentations.

**50 ft. Cable Lets You Design an Audio/Video Application to Your Specifications** This long HDMI cable allows you greater flexibility in placing your home theater or digital signage components. For instance, your Blu-ray player or media server may be concealed some distance from the connected display for security purposes.

### Highlights

- 50 ft. length allows great flexibility in placing home theater or digital signage devices
- Supports UHD resolutions up to 4096 x 2160 (@ 30 Hz) for crystal-clear 4K x 2K video
- CL2-rated PVC cable jacket meets required standards for in-wall installation
- Foil/braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Plug-and-play operation with no booster required for easy, immediate installation

### Applications

- Watch 4K video from a Blu-ray player, game console, laptop or tablet on an Ultra HD television, monitor or projector
- Connect a Chromebook or MacBook to a conference table's A/V box to give a video presentation on a large screen
- Play online or PC video games that display optimal graphics
- Combine with an Apple digital A/V adapter to support iPad2 video mirroring
- Send 4K video content via in-wall cable setups to digital signs or point-of-sale displays

### Package Includes

P568-050-HD-CL2 High-Speed HDMI Cable, CL2 Rated, M/M, Black, 50 ft.

## Specifications

### OVERVIEW



|  |                            |
|--|----------------------------|
| UPC Code                                     | 037332252845               |
| Product Type                                 | Passive                    |
| Technology                                   | HDMI                       |
| <b>VIDEO</b>                                 |                            |
| Max Supported Video Resolution               | 4096 x 2160 @ 30 Hz        |
| HDR Support                                  | No                         |
| 3D Video Supported                           | No                         |
| <b>INPUT</b>                                 |                            |
| Product Length (in.)                         | 600                        |
| Product Length (ft.)                         | 50                         |
| <b>PHYSICAL</b>                              |                            |
| Color  | Black                      |
| Material of Construction                     | PVC                        |
| Cable Jacket Material                        | PVC                        |
| Cable Jacket Rating                          | CL2; VW-1                  |
| Cable Outer Diameter (OD)                    | 10.0                       |
| Wire Gauge (AWG)                             | 24                         |
| Cable Length (ft.)                           | 50                         |
| Cable Length (in.)                           | 600                        |
| <b>ENVIRONMENTAL</b>                         |                            |
| Operating Temperature Range                  | 0 - 45 °C (32 - 115 °F)    |
| Storage Temperature Range                    | -40 - 80 °C (-40 - 176 °F) |
| Relative Humidity                            | 5 - 90 %, NON-CONDENSING   |
| <b>COMMUNICATIONS</b>                        |                            |
| Consumer Electronics Control (CEC) Supported | No                         |
| <b>CONNECTIONS</b>                           |                            |
| Side A - Connector 1                         | HDMI (MALE)                |
| Side B - Connector 1                         | HDMI (MALE)                |
| Connector Plating                            | Gold                       |
| Contact Plating                              | Gold                       |



| <b>FEATURES &amp; SPECIFICATIONS</b>        |                           |
|---|---------------------------|
| HDCP Specification                          | 1.4                       |
| Fully Molded Connector Ends                 | No                        |
| Ohms  | No                        |
| EMI/RFI Line Noise Protection               | No                        |
| Integral Strain Relief                      | No                        |
| Impedance-Matched Twisted-Pair Construction | No                        |
| DIN Mountable                               | No                        |
| Integrated/Removable Cable                  | No                        |
| MST Support                                 | No                        |
| Scaler Function                             | No                        |
| IP67 Rated                                  | No                        |
| Fire Rating                                 | CL2 Rated                 |
| <b>STANDARDS &amp; COMPLIANCE</b>           |                           |
| Certifications                              | Tested to RoHS and REACH  |
| <b>WARRANTY</b>                             |                           |
| Product Warranty Period (Worldwide)         | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>