

Coaxial Cable Connector 16_SMA-50-4-55/199_N

Description

Right angle cable plug

Interface standards

IEC 60169-15_MIL-STD-348A/310_CECC 22110

Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 18 GHz

Mechanical Data

Centre contact plugged
Outer contact crimped
Weight 0.0093 kg

Environmental Data

Operating temperature -65 °C to 125 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Other body part	Stainless Steel	
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Stainless Steel	
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) / SUCOPRO Plating

Related Documents

Outline drawing DOU-00007764
Assembly instruction DOC-0000201296

Ordering Information

Single package 16_SMA-50-4-55/199_NE

Additional Information

Suitable cables S_04212_B