



**Specification**

Insulator Material: Polyseter, UL94V-0

Standard: PA6T

Contact Material: Brass

Contact plated: Gold Over Nickel

Poles: 2~40P

Current Rating : 3Amp

Insulation Resistance : 1000MΩ Min.

Dielectric withstanding Voltage: AC 500V

Operation Temperature : -40℃ -- +105℃

**TOLERANCE TABLE**

|      |       |
|------|-------|
| .0   | ±0.20 |
| .00  | ±0.10 |
| .000 | ±0.05 |

|                  |                   |   |
|------------------|-------------------|---|
| <b>APPROVED:</b> | <b>DATE:</b>      | <b>深圳市灿科盟实业有限公司</b><br><b>CHANKEMENG INDUSTRYCO., LTD</b>   |
| <b>CHECKED:</b>  | <b>DATE:</b>      |   |
| <b>DRAM:</b>     | <b>DATE:</b>      | <b>210S-1*4P 双翅 L=11.6mm (3.6/5.0/3.0)</b><br>CLIENT P/N C2902691<br>UNIT mm SCALE Free<br>FILE NO. B-2100S04P-C000 |
| <b>YAN</b>       | <b>2012-05-15</b> |   |
|                  |                   | REV. A  |