**ROCKER SWITCHES - ILLUMINATED** 



#### **SPECIFICATIONS**

Contact Rating\*: Versions D,G,I - 10A @ 250V, 15A @ 125VAC Versions A,B,C,E,F,H,J-16A @ 250V, 20A @ 125VAC

Life Expectancy (Mechanical): 30,000 cycles

Life Expectancy (Electrical): 6,000 cycles

Contact Resistance: 20 mΩ max. typical initial @ 2-4 VDC

Insulation Resistance: >1,000MΩ

Dielectric Strength: >1,500V 1 minute between terminals

Safety Std. Approval: UL, VDE

Operating Temp: -20°C to 55°C

#### **FEATURES & BENEFITS**

- ► Fully illuminated actuator option
- Neon & incandescent lamp options

#### APPLICATIONS/MARKETS

▶ Industrial

R4-B-BLK-BLK-YEL-E-F-2

- ► Audio/visual
- ► Lighting ballast

R4	CIRCUIT	HOUSING COLOR	ACTUATOR COLOR	DOT LENS COLOR	MARKING	TERMINATION	LAMP VOLTAGE
	C = SPDT On-Oi  D = SPDT On-Oi  E = SPDT On-IO  F = SPST Off-IO  G = SPDT (On)-I  H = SPST On-IO  I = SPDT On-Oi	ff Dot Illuminated n ff-On on On Off-(On)	BLK = Black RED = Red RIL = Red ILL GIL = Green ILL YIL = Yellow ILL	RED = Red ** GRN = Green ** YEL = Yellow **	A B C D E F G H L J K L	F = Faston	0 = No Lam 1 = 125V A( 2 = 250V A( 3 = 12V DC 4 = 24V DC  1 Neon Bulb 2 LED

•• To be used with the "B" circuit only

Specifications subject to change without notice. 2/6/2020

\* To be used with the "J" circuit only

# **SERIES R4 SWITCHES**


## **ROCKER SWITCHES - ILLUMINATED**


#### SPST





Circuit Code	POS 1	POS 2
А	ON	OFF
В	ON	OFF
F	(ON)	OFF
Н	ON	(OFF)
J	ON	OFF
Term. Comm.	1-1a	OPEN


( ) = Momentary











Fax: 763-531-8235

### SPDT



Circuit Code	1081	₩	1033
С	ON	NONE	ON
D	ON	OFF	ON
E	ON	NONE	(ON)
G	(ON)	OFF	(ON)
I	ON	OFF	(ON)
Term. Comm.	1-1a	OPEN	1-1b

( ) = Momentary



NOTE: Illumination not available for SPDT versions.


#### **Panel** X **Thickness** .75-1.25 29.65 ± .05 11.15 ± .05 Panel Cut Out (.439 ± .002 in) [.028-.049 in] [1.167 ± .002 in] 1.25 - 2.00 30.15 ± .05 [.049 - .079 in] [1.187 ± .002 in] 2.00 - 3.00 30.50 ± .05 [.079 - .118 in] [1.201 ± .002 in]

PANEL MOUNTING

#### **TERMINATION OPTIONS**



#### **MARKING OPTIONS**



170

Phone: 800-867-2717