


PRODUCT NUMBER: 3137-1-00-21-00-00-08-0

313X-X-00-XX-00-00-08-0

Solder mount in .043 min. mounting hole

Click on image carousel below for additional details



Standard Tolerances:
 Lengths: ±.005
 Diameters: ±.002
 Angles: ± 2°

Basic Part Number	Board Thickness	Length (V)	Flange Dia. (C)
3136-1	.062	.082	.078
3136-2	.094	.110	
3136-3	.125	.145	
*3137-1	.062	.082	.062
3137-2	.094	.110	
3137-3	.125	.145	
3137-4	.156	.185	

* Available packaged on Tape & Reel


3137-1-00-XX-00-00-08-0

Solder mount in .043 mounting hole

Also available on 16mm wide X 12mm pitch carrier tape:

580 parts per 13" reel

Order as: 3137-1-57-XX-00-00-08-0



Standard Tolerances:
 Lengths: ±.005
 Diameters: ±.002
 Angles: ± 2°

DESCRIPTION

Solder Mount PCB Pin

Current Rating:

Application Specific

Operating Temperature Range:

-55/+125° C (discontinuous)

Mounting Feature:

Through Hole Solder Mount

Tail Type: Soldertail

Mounting Hole: .043" (1,092mm)

Tail Diameter: .030" (0,762mm)

Packaging: 00 - Packaged in Bulk

Shell Plating	Contact Plating	ROHS
----------------------	------------------------	-------------

20 μ" Gold over Nickel



ADDITIONAL NOTES & SPECIFICATIONS

In the interest of improved design, quality and performance, Mill-Max reserves the right to make changes in its specifications without prior notice. Specifications and tolerances are provided wherever possible. Due to the wide variety of interconnects Mill-Max offers, the specific tolerances vary from product to product. If you need information regarding the tolerance of a particular part, please contact Technical Services.

