


Self-aligning ball bearings, cylindrical and tapered bore



Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
40	90	23	33,8	11,2	0,57	14000	9500	0,68	1308 ETN9



Calculation factors

- e 0,23
- Y_1 2,7
- Y_2 4,2
- Y_0 2,8