

- Back**
- o Flat Cable Connectors SEK
 - o *har-mik®*
 - o D-Sub
 - o InduCom

- **Applications**

Product details

09 56 500 4701 **High density cable connector**

Gender	Female High Density
Termination	Crimp
Number of contacts	78
Flange	through hole 3.1 mm
Shell	tinned metal shell
Insulation material	PBTP
Contact configuration	contacts must be order separately
RoHS compliant	Yes




Inquiry



Available Downloads

Title	Format	
Data sheet	PDF	download
CAD data 2D	DXF	download

Product news

5 4 3 2 1



				Det.	16-SEP-02	CV	 All Dim. in mm Orig. Size DIN A 4	D-Sub, High density, female, 78 poles, for crimp contact	Maßstab/ Scale
			Insp.			115t1			
			Stand.						
31064	16-SEP-02	CV	HARTING EURL F-95972 Paris				TB 09565004701	Blatt/ Page	
Mod.	Det.	Name					Sub.	1	