This document was generated on 04/08/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0430300002
Status: Active
Overview: Micro-Fit Connector System
Description: Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 20-24 AWG, Reel

Series image - Reference only

Documents:

Drawing (PDF)
Product Specification PS-43045-001 (PDF)
Packaging Specification PK-43030-001-001 (PDF)
Test Summary 430450005-TS-000 (PDF)
Test Summary 430450006-TS-000 (PDF)
Test Summary TS-43045-001-001 (PDF)
Test Summary TS-43045-002-001 (PDF)
Datasheet (PDF)
RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	43030
Application	Power, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Micro-Fit Connector System
Packaging Alternative	430300008 (Loose)
Product Name	Micro-Fit 3.0
UPC	800753683662

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.062/g
Packaging Type	Reel
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.85mm max.
Wire Size AWG	20, 22, 24
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	8.5A

Solder Process Data

Lead-freeProcess Capability	N/A

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-43030-001-001
Product Specification	PS-43045-001
Sales Drawing	SD-43030-XXXX-001
Test Summary	430450005-TS-000, 430450006-TS-000, TS-43045-001-001, TS-43045-002-001

EU ELV
Compliant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per - ECHA_01_2020 (16 January 2020

Halogen-Free Status
Low-Halogen

For more information, please visit Contact US

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
43030 Series

Use With
Micro-Fit 3.0 Receptacle Housings 43025 , 43645
Micro-Fit BMI Panel Mount Receptacle Housings 44133 , 46623
Micro-Fit TPA Receptacle Housing 171850 , 172952

Application Tooling | **FAQ**

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool Insertion Tool for Micro-Fit 3.0 and CRC Male and Female Crimp Terminals, 20-30 AWG	11030043 638120800

Downloaded from Arrow.com.

Hand Crimp Tool	638190000
FineAdjust Applicator for Insulation OD 1.30-1.85mm, 20-24 AWG Wire	639004500
FineAdjust Applicator for Insulation OD 1.10-1.30mm - 20-24 AWG	639018800
FineAdjust Applicator for Insulation OD 0.91-1.09mm - 20-24 AWG	639018900
T2 Terminator for Insulation OD 1.30-1.85mm, 20-24 AWG	639104500
T2 Terminator for insulation OD 1.10-1.30mm - 20-24 AWG	639118800
T2 Terminator for insulation OD 0.91-1.09mm - 20-24 AWG	639118900

Japan

Description	Product #
Applicator for M211A Bench Press, 20-30 AWG Wire	572983000
S-1 Applicator for Micro-Fit 3.0 Plug and Receptacle Crimp Terminals, 20-24 AWG	572983700

Downloaded from Arrow.com.