

Slide Switch

Q-9907




TYPE: **SK-13D45**




SPECIFICATIONS

Contact Type	SPDT
Pin Width	2mm
Rating	DC 50V, 0.3A
Contacts Resistance	30mΩ
Insulation Resistance	100MΩ
Minimum Load	DC 500V
Dielectric Strengths	AC 500V / 1 minute
Life Test	10 000 cycles/ minute
Material	Plastic & Metal

Outline Drawing



Mounting



Circuitry

