

80X80X38 mm

JA0838-0N Series



- **Motor** : Two-pole shaded pole induction motor
- **Frame** : Aluminum Alloy, Painted black
- **Impeller** : Retardant thermoplastic in black color, rated UL94V-0
- **Speed Range** : $\pm 10\%$
- **Impedance protected**

SPECIFICATIONS

Model	Bearing	Nominal Voltage (V)	Frequency (Hz)	Air Flow (CFM)	Static Pressure (inchH ₂ O)	Speed (R.P.M.)	Nominal Current (Amp)	Input Power (Watt)	Noise (dBA)	Weight (g)
JA0838H1B0N	Dual Ball	110 - 120	50	21.42	0.102	2400	0.17	13	25.2	285
			60	26.46	0.149	2800		10	32.1	
JA0838H1S0N	Sleeve		50	20.78	0.098	2200		13	24.4	
			60	25.19	0.134	2600		10	30.0	
JA0838H2B0N	Dual Ball	220 - 240	50	22.25	0.109	2400	0.08	12	26.3	
			60	26.74	0.152	2800		9	31.9	
JA0838H2S0N	Sleeve		50	20.44	0.094	2200		12	24.2	
			60	24.19	0.122	2500		9	28.2	

Specifications subject to change without notice

