



Fuse-link, LV, 40 A, AC 500 V, BS88/A4, 25 x 110 mm, gL/gG, BS

Catalog No. CE040

### Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	40
Rated voltage			AC 500 V
Construction size			BS88/A4
Size			25 x 110 mm
Utilization category			gL/gG
Breaking Capacity		kA	80
usable for size/applications			general industrial applications
Standard/Approval			BS
Shape			offset bolted tags
Standards/Regulations			BS88-2 IEC 60269-2
Optional accessories			fuse-holder RS100H

### Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	40
Rated voltage		V	550
Voltage type			AC
Rated switching capacity		kA	80
Utilization category			gL/gG (cable protection/equipment protection)
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No

### Additional product information (links)

Product datasheet (pdf)	<a href="http://www1.cooperbusmann.com/pdf/9bcad827-3ad7-413d-b71a-5fe7ac0da2cc.pdf">http://www1.cooperbusmann.com/pdf/9bcad827-3ad7-413d-b71a-5fe7ac0da2cc.pdf</a>
-------------------------	---