



## Hexagon Metric, 6700SM

Hexagon socket in Metric sizes.

DIN 3124/ISO 2725.

1/4" 6.3 DIN 3120/ISO 1174.






**Finish:** nickel and chrome-plated, fine-polished.

**Material:** CHROMO-EXTRA.

With Dynamic-Drive-Profile.

**SB** = Retail packed on a plastic info card.



				L mm	D1 mm	D2 mm 
6700SM-4	1087944	5	4	22.2	6.7	12.1 9
6700SM-4.5	1087951	5	4.5	22.2	7.2	12.1 10
6700SM-5	1087968	5	5	22.2	7.7	12.1 10
6700SM-5.5	1087975	5	5.5	22.1	8.3	12.1 10
6700SM-6	1087982	5	6	22.3	9.3	12.1 10
6700SM-7	1087999	5	7	22.2	10.5	12.1 12
6700SM-8	1088002	5	8	22.2	11.5	12.1 12
6700SM-9	1088019	5	9	22.2	12.7	12.1 12
6700SM-10	1088026	5	10	22.2	14.0	12.1 15
6700SM-11	1088033	5	11	22.2	15.4	13.1 18
6700SM-12	1088040	5	12	22.2	16.5	14.0 18
6700SM-13	1088057	5	13	22.2	17.6	15.0 20
6700SM-14	1088064	5	14	23.0	18.8	16.0 22
SB6700SM-4	0104307	1	4	22.2	6.7	12.1 9
SB6700SM-4.5	0104314	1	4.5	22.2	7.2	12.1 10
SB6700SM-5	0104321	1	5	22.2	7.7	12.1 10
SB6700SM-5.5	0104338	1	5.5	22.1	8.3	12.1 10
SB6700SM-6	0104345	1	6	22.3	9.3	12.1 10
SB6700SM-7	0104352	1	7	22.2	10.5	12.1 12
SB6700SM-8	0104369	1	8	22.2	11.5	12.1 12
SB6700SM-9	0104376	1	9	22.2	12.7	12.1 12
SB6700SM-10	0104383	1	10	22.2	14.0	12.1 15
SB6700SM-11	0104390	1	11	22.2	15.4	13.1 18
SB6700SM-12	0104406	1	12	22.2	16.5	14.0 18
SB6700SM-13	0104413	1	13	22.2	17.6	15.0 20
SB6700SM-14	0104420	1	14	23.0	18.8	16.0 22