

Cable trunking miniature plain with base punching




GI-M



GI-M

Material:	rigid PVC modified choc
Colour:	white (RAL 9001)
Operating temperatures:	-20 to +60°C
Density:	1,53
Volume resistivity:	10 ¹⁴ Ω.cm
Dielectric strength:	15kV/mm
Specification:	V0 UL94
Standard length:	2 meters
Minimum quantity:	1 complete pack (with hinged lid)



GI-M miniature trunking are extruded in one piece. They are available with hinged lid and with or without adhesive foam tape. Foam tape is ideal for absorbing the irregularities on uneven surfaces. For some applications, we recommend further attachment with screws and wall plugs.

type	article number	ext. dimensions		Ø D mm	 m
		H mm	W mm		
GI-M 5 x 10 T	0846 0911 001	6	11	2,2	48
GI-M 7 x 12 T	0846 0921 001	8	13	2,2	48
GI-M 10 x 10 T	0846 0931 001	11	11	2,2	48
GI-M 10 x 15 T	0846 0941 001	11	16	3,2	48
GI-M 15 x 15 T	0846 0951 001	16	16	3,2	48

