



SOLUTIONS

PRODUCTS AND SERVICES

SUPPORT

ABOUT US

Search Panduit.com

GO



Search within category

GO

BUY NOW

DESIGN / INSTALL

**PCSB2/0-3S-6Y**

Multi-Tap connector, single-sided, clear insulation, 3 ports, 2/0 - #14 STR.

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

| | |
|--|--|
| Material | Aluminum / Clear PVC |
| Overall Height (In.) | 1.4 |
| Overall Height (mm) | 35.1 |
| Conductor Material | Copper and Aluminum |
| Product Type | Multi-Tap Mechanical Connectors, Single Sided |
| Copper and Aluminum Conductor Size Range | 2/0 - #14 AWG STR #10 - #14 AWG SOL |
| Number of Ports | 3 |
| Stud Hole Size In. (mm) | NA |
| Height 1 In. (mm) | — |
| Height 2 In. (mm) | — |
| Hex Key Size (In.) | 3/16 |
| Length In (mm) | 2.19 (55.6) |
| Mounting Hole Spacing In. (mm) | — |
| NEMA Hole Spacing | — |
| Width In (mm) | 1.31 (33.3) |
| CSA Certified | C22.2 No. 65-13 |
| Maximum Output Voltage (V) | — |
| Tin-Plating Meets ASTM B545-97, Class C | 320μ-in (8 μm) |
| UL Listed | 486A-486B File #E52164 |
| UL Temperature Rating | — |
| UL and CSA Temperature Rating | 90°C |
| UL and CSA Voltage Rating | 600V |
| Insulation Material | Clear PVC |
| Part Number Series | PCSB |
| Includes | Each port pre-filled with oxide inhibiting joint compound |
| Part Features | Each port pre-filled with oxide inhibiting joint compound seals out air and moisture to deter surface oxidation. |
| RoHS Compliancy Status | Compliant |
| Min. Order Qty. | 1 |
| Sub Brand | Pan-Lug |

