

General Description

Series	597
Configuration	'0805(2.0MM X 1.25MM X 0.7MM)
Description	SMD LED 0805 G 7" Reel
Package Options	Tape and Reel
Lamp Type	Single Color
Lens Color	Non - Diffused

Absolute Maximum Ratings (Ta = 25Å °)

Forward Current mA	30mA
Reverse Current	100 @ Vr =5V
Forward Current Pulsed	100mA
Derating	from 50Å° @ .6mA/Å°C
Solder Temperature	260Å° for 5 sec
Operating Temperature	-55~+100
Storage Temperature	-55~+100

Operating Characteristics

Color	Gre
Luminous Intensity Min	4
Luminous Intensity Typical	8
Test Current mA	-
Power Dissipation Max	114

- [Site Map](#)
- [Contact Us](#)
- [Dialight BLP Ltd](#)
- [Privacy Policy](#)
- [C](#)