

datasheet for AGF 20
 article number: 930120000



product description:	order number: 930 120-000
description:	Nickel-plated steel alligator clip. The special shape allows clamping of both extremely fine and thick wires. 4 mm diameter socket connection and solder connection possible. max. bolt diameter 12 mm
typ:	AGF 20
system:	4mm system
order number:	930 120-000
clamping range:	10 mm
technical data	
measurement category acc. to IEC 61010:	CAT I
norm	IEC 61010
type of contact:	clamp
type of termination:	4 mm socket (unsprung), solder
rated voltage:	30 VAC / 60 VDC
rated current:	4 A
Please consider derating curve!	
contact resistance:	10 mOhm
material	
contact material:	steel
contact surface material:	nickel
environmental conditions:	
temperature range:	-25 °C to +100 °C
drawing	
	