

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200490457](#)
Status: **Active**
Overview: Brad® Ethernet Solutions
Description: Micro-Change (M12) Double-Ended Cordset, 4 Poles, Male (Straight) to Male (Straight), 24 AWG, PVC Cable, 80.0m (262.40') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E200650

General

Product Family Industrial Cordsets
 Series [120049](#)
 Connector End A Micro-Change (M12)
 Connector End B Micro-Change (M12)
 IP Rating IP67
 Material - Contact Copper Alloy
 Overview [Brad® Ethernet Solutions](#)
 Performance Category 5e
 Product Name Micro-Change (M12)
 Region America, Asia, Europe
 Type Double Ended
 UPC 883906170134

Physical

Cable Diameter 6.35mm (.250")
 Cable Length 80.0m (262.40')
 Color - Cable Jacket Blue Green
 Coupling Style Threaded
 Gender Male-Male
 Keyway D-coded
 LED Indicator No
 Material - Cable Jacket PVC
 Material - Connector Body TPU
 Material - Coupling Nut Nickel-plated Brass
 Material - O-Ring Fluoro-elastomer
 Material - Plating Mating Gold over Nickel
 Orientation Straight to Straight
 Poles 4
 Temperature Range - Operating -25°C to +75°C
 Wire Size AWG 24
 Wire/Cable Type Unshielded-Stranded

Electrical


Current - Maximum per Contact 1.5A
 Voltage - Maximum 125V

Material Info

Engineering Number E11A06002M800

Reference - Drawing Numbers

Sales Drawing SD-120049-001-001



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per -ED/88/2018 (15 January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[120049 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION