



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT3I	.06 (1.5)	3.00 (76)	.052 (1.3)	.145 (3.7)	.220 (5.6)	.180 (4.6)	.260 (6.6)	11.4 (290)	40 (178)	INTERMEDIATE	CURVED	.32 (145)
PLT4I	.06 (1.5)	4.00 (102)	.052 (1.3)	.145 (3.7)	.220 (5.6)	.180 (4.6)	.260 (6.6)	14.5 (368)	40 (178)	INTERMEDIATE	CURVED	.40 (181)
PLT1S	.06 (1.5)	1.00 (25)	.052 (1.3)	.190 (4.8)	.262 (6.7)	.220 (5.6)	.316 (8.0)	4.8 (122)	50 (222)	STANDARD	CURVED	.13 (58)
PLT1.5S	.06 (1.5)	1.50 (38)	.052 (1.3)	.190 (4.8)	.262 (6.7)	.220 (5.6)	.316 (8.0)	6.2 (157)	50 (222)	STANDARD	CURVED	.26 (118)
PLT2S	.06 (1.5)	1.88 (47.8)	.052 (1.3)	.190 (4.8)	.262 (6.7)	.220 (5.6)	.316 (8.0)	7.4 (188)	50 (222)	STANDARD	CURVED	.29 (132)
PLT2.5S	.06 (1.5)	2.50 (63.5)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	9.8 (249)	50 (222)	STANDARD	CURVED	.38 (173)
PLT3S	.06 (1.5)	3.00 (76)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	11.5 (292)	50 (222)	STANDARD	CURVED	.45 (204)

NOTES:

*SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	ITEM REVISION NAME	DATASET FILE NAME	MATERIAL:	DRAWING NUMBER:
							PAN-TY CABLE TIES - PLT SERIES				
							CUSTOMER DRAWING				
								W10001CB/32		PANDUIT	
									W10001CB/32 SS-5540 SH2_REV32		
									UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		
									.x ± .005	.xxx ± .020 (.51)	
									.xx ± .02 (.5)	ANGLES ± .005	
									THIRD ANGLE PROJECTION		
32	10/01/15	BWG	MPH	JADE	REVISED NOTES.	SS-5540/32					
31	8/13/13	BWG	KJM	RTFI	CORRECTED REV NO. REMOVED NOTE 1. SEE ECN FOR DETAILS.	SS-5540/30					SS-5540 SHEET 2
							DRAWN BY	DATE	CHK	SCALE	SIZE
							CEW	12-27-84	HVP	NONE	A
											SHT 1 OF 1