



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
H	-	A	INITIAL RELEASE	29NOV2013	YC	BvH
		A1	ECR-14-015049	13OCT2014	GSK	BvH

NOTES:
 Tolerances cable lengths:
 0m to 0.5m +30mm
 0.5m to 1.0m +50mm
 1.0m to 3.0m +100mm
 < 3.0m +1.5%



TECHNICAL DATA	
Operating voltage	max. 250 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M12 x 1 mm (recommended torque 0.6 Nm) self-securing
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)



PUR CABLE	
No./diameter of wires	4 x 0.34 mm ²
Wire isolation	PP (br, wh, bl, bk)
C-track properties	5 million
Jacket	PUR (UL/CSA)
Outer diameter	approx. 4.7 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	-40...+80 °C
Temperature range (mobile)	-25...+80 °C

LENGTH "L"	MATERIAL	JACKET COLOR	TE PN	DESCRIPTION	ITEM
4 pos	PVC	Black	1-2273113-5	4x22AWG PVC 2.0m	10
			1-2273113-4	4x22AWG PVC 1.5m	9
			1-2273113-3	4x22AWG PVC 1.0m	8
			1-2273113-2	4x22AWG PVC 0.6m	7
			1-2273113-1	4x22AWG PVC 0.3m	6
4 pos	PUR	Black	2273113-5	4x22AWG PUR 2.0m	5
			2273113-4	4x22AWG PUR 1.5m	4
			2273113-3	4x22AWG PUR 1.0m	3
			2273113-2	4x22AWG PUR 0.6m	2
			2273113-1	4x22AWG PUR 0.3m	1

PVC CABLE	
No./diameter of wires	4 x 0.34 mm ²
Wire isolation	PVC (br, wh, bl, bk)
C-track properties	
Jacket	PVC (UL/CSA)
Outer diameter	approx. 5.0 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	-30...+80 °C
Temperature range (mobile)	-5...+80 °C

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	YATHISH.C	29NOV2013	TE Connectivity M12 STRGT PLUG TO M12 STRGT SOCKET AA			
CHK	B.VELDHOVEN	29NOV2013				
APVD	A.VAN ZANDVOORT	29NOV2013				
NAME						
PRODUCT SPEC	108-19483		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
APPLICATION SPEC	114-32127		A3	00779	C-2273113	-
MATERIAL	FINISH	WEIGHT	CUSTOMER DRAWING		SCALE	SHEET
-	-	-			NTS	1 OF 1
					REV	A1