

Suspension TP E27 80CM Black

Article number 141258

BAI Suspension Black 80cm Round cable 2x0.75mm² with Thermoplastic Lampholder E27 and Conical Ceiling Cup



General ETIM properties

ETIM group	Luminaires
ETIM class	Pendant luminaire
Name	Suspension TP E27 80CM Black
Brand	Bailey
Productseries	Pendant Light Set
Product type	Pendelarmatuur
GTIN	08714681412589
Manufacturer articlenumber	141258

ETIM specifications

Suitable for light line configuration	No
Fit for monitor workplace acc. EN 12464-1	No
Lamp type	Incandescent lamp
With light source	No
Suitable for number of lamps	1
Lamp holder	E27
Material housing	Plastic
Colour housing	Black
Material cover	Without cover
Type of grid	None
Voltage type	AC
Nominal voltage [V]	220 - 220
Type of control gear	Not required
Control gear included	No
Dimming 0-10 V	No
Dimming 1-10 V	No
Dimming DALI	No
Dimming DMX	No
Dimming programmable	No
Dimming DSI	No
Dimming RF	No
Dimming potentiometer (integrated)	No
Dimming GPRS	No
Dimming LineSwitch	No
Dimming manufacturer's proprietary system	No
Dimming mains voltage modulation	No
Dimming phase cut-off	No
Dimming phase cut-on	No

Dimming Sine Wave Reduction	No
Dimming Touch and Dim	No
Dimming Zigbee	No
Dimming with push-button	No
No dim function	Yes
Reflector	None
Light sharing	Symmetric
Light outlet	Direct
Direct-/indirect proportion separately controllable	No
Degree of protection (IP)	IP20
Impact strength	IK00
Protection class	II
Luminaire with limited surface temperature, sign "D"	No
Suitable for emergency lighting	No
Filament test according to IEC 60695-2-11	None
Suitable for lamp power [W]	60 - 60
Rated luminous flux acc. IEC 62722-2-1 [lm]	0
Width [mm]	0
Height/depth [mm]	0
Length [mm]	912
Diameter [mm]	110
Suspension supplied with the product	Yes
Pendant length [mm]	800 - 800
Type of wiring	Suitable for through wiring
Number of poles	2
Conductor cross section [mm ²]	0.75