


QuantX™ Blunt End Plastic Hub Needles

A full selection of UV-bonded dispense tips manufactured with polypropylene hubs and stainless steel cannulas. Double helix Luer lock design and polished burr-free finish ensure precision fluid dispensing. For dispensing low to high viscosity fluids in general purpose dispense applications. The long tube design allows for fluids to be easily dispensed into hard to reach areas which conventional dispense tips cannot reach.



Color	Gauge	I.D. (inch)	I.D. (mm)	2"	3"	4"	5"
Navy Blue	12	0.089	2.27	8001314	8001330	8001341	8001351
Magenta	13	0.070	1.78	8001315	8001331	8001342	8001352
Olive	14	0.063	1.60	8001316	8001332	8001343	8001353
Amber	15	0.054	1.37	8001317	8001333	8001344	
Black	16	0.047	1.20	8001318	8001334	8001345	
White	17	0.041	1.04	8001319	8001335	8001346	
Green	18	0.033	0.84	8001320	8001336	8001347	
Brown	19	0.028	0.70	8001321	8001337	8001348	
Pink	20	0.024	0.60	8001322	8001338	8001349	
Purple	21	0.020	0.51	8001323	8001339	8001350	
Blue	22	0.016	0.41	8001324	8001340		
Orange	23	0.013	0.33	8001325			
Sky Blue	24	0.012	0.31	8001326			
Red	25	0.010	0.25	8001327			
Beige	26	0.009	0.23	8001328			
Clear	27	0.008	0.20	8001329			

QuantX™ Single Tapered Dispense Tips

Tapered smooth flow dispensing tips are designed to reduce back pressure of high-viscosity fluids resulting in an increased fluid flow rate. A uniform polypropylene Luer lock design with a flash-free outlet ensures consistent fluid dispensing.



Standard Single Tapered UV Blocking

Color	Gauge	I.D. (inch)	I.D. (mm)	Length (inch/mm)	Item Number
Lime Green	10	0.118	3.00	1.25/32	8001217
Yellow	11	0.098	2.50	1.25/32	8001218
Sky Blue	13	0.079	2.00	1.25/32	8001219
Olive	14	0.063	1.60	1.25/32	8001269
Amber	15	0.054	1.37	1.25/32	8001220
Gray	16	0.047	1.20	1.25/32	8001270
Green	18	0.033	0.84	1.25/32	8001271
Pink	20	0.024	0.60	1.25/32	8001272
Purple	21	0.020	0.51	1.25/32	8001221
Blue	22	0.016	0.41	1.25/32	8001273
Orange	23	0.013	0.33	1.25/32	8001222
Red	25	0.010	0.25	1.25/32	8001274
White	27	0.008	0.20	1.25/32	8001298
Lavender	30	0.006	0.15	1.25/32	8001276