

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0393570002](#)  
**Status:** **Active**  
**Overview:** Eurostyle Terminal Blocks  
**Description:** 3.50mm Pitch Beau Eurostyle Fixed Mount PCB Terminal Block, 2 Circuits

**Documents:**

[3D Model \(PDF\)](#)                      [Drawing \(PDF\)](#)  
[3D Model](#)                                [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL                                              E48521

**General**

Product Family                              Terminal Blocks  
Series                                              [39357](#)  
Application                                      N/A  
Component Type                                One Piece  
Overview                                         [Eurostyle Terminal Blocks](#)  
Product Name                                  Eurostyle Fixed Mount  
Type                                                Euro Block  
UPC                                                 756054634127

**Physical**

Circuits (Loaded)                              2  
Circuits (maximum)                            2  
Entry Angle                                      Horizontal  
Flammability                                    94V-0  
Lock to Mating Part                            None  
Net Weight                                       1.240/g  
Number of Rows                                1  
Orientation                                       Vertical  
PC Tail Length                                  3.50mm  
PCB Retention                                  None  
PCB Thickness - Recommended              1.60mm  
Panel Mount                                      No  
Pitch - Mating Interface                       3.50mm  
Pitch - Termination Interface               3.50mm  
Polarized to Mating Part                      No  
Shrouded                                         Fully  
Stackable                                         Yes  
Surface Mount Compatible (SMC)            No  
Temperature Range - Operating              -30° to +85°C  
Wire Size AWG                                  16, 18, 20, 22, 24, 26, 28  
Wire Size mm<sup>2</sup>                                  0.20-1.00

**Electrical**


Current - Maximum per Contact              17.5A  
Voltage - Maximum                              300V

**Material Info**

Engineering Number                            MX-MTB02008-0N

**Reference - Drawing Numbers**

Sales Drawing                                    SD-39357-001-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per -  
D(2021)4569-DC (8  
July 2021)

Lead

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[39357 Series](#)

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39357-0002](#)