

Number of contacts

2



Identification	Part-Number		Drawings	Dimensions in mm
	Male insert (M)	Female insert (F)		
Han® 70 A module Crimp terminal	09 14 002 3041	09 14 002 3141		

Han Modular

Identification	Wire gauge mm ²	Part-Number		Drawings	Dimensions in mm												
		Male contacts (M)	Female contacts (F)														
Crimp contacts* Silver plated					<table border="1"> <thead> <tr> <th>Wire gauge</th> <th>Ø</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>10 mm²</td> <td>4.3</td> <td>15.5 mm</td> </tr> <tr> <td>16 mm²</td> <td>5.5</td> <td>15.5 mm</td> </tr> <tr> <td>25 mm²</td> <td>7.0</td> <td>15.5 mm</td> </tr> </tbody> </table> <p>for stranded wires acc. to IEC 60 228 class 5</p>	Wire gauge	Ø	Stripping length	10 mm ²	4.3	15.5 mm	16 mm ²	5.5	15.5 mm	25 mm ²	7.0	15.5 mm
Wire gauge	Ø	Stripping length															
10 mm ²	4.3	15.5 mm															
16 mm ²	5.5	15.5 mm															
25 mm ²	7.0	15.5 mm															
	10	09 11 000 6131	09 11 000 6231														
	16	09 11 000 6132	09 11 000 6232														
	25	09 11 000 6133	09 11 000 6233														

* Crimp zone acc. to DIN EN 46 235

Stock items in bold type