

F

E



D

C

B

A

RoHS STANDARD



Technical requirement :

- 1 . This product should meet EU RoHS related requirement.
- 2 . The surface of plastic part should be without any crackle such as burr,lack,and so on phenomenon.
- 3 . The surface of metal part should be without any defect such as scour,nick,oxidation and plating problem.
- 4 . The electronic performance should be the same as spec.

Specification :

- Contact Resistance : 30m ohm max.
 Insulation Resistance : 100M ohm min. at DC 500V
 Dielectric Resistance : AC 500V for one minute.

DCI DRAGON CITY INDUSTRIES LIMITED

PART NAME DC PLUG (3.1 x 6.3mm) TOLERANCE : \pm

PART NO. NP-125-EN-HY UNIT: MM

DESIGN	K.W LAW	REMARK		SCALE	
DRAWING	W.K YEUNG	REMARK		MATERIAL	
CHECK	K.L WONG	REMARK		DWG. NO.	B201171505
APPROVAL	K.W CHAN	REMARK		SHEET	

F

E

D

C

B

A