

**W-Series
WAP WDK2.5/4 N**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The versatile and extensive range of products - from 0.05 mm² to 300 mm² - means that you have diverse options for your applications at your disposal.

Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

General ordering data

Type	WAP WDK2.5/4 N
Order No.	1084000000
Version	W-Series, End plate
GTIN (EAN)	403224812735 1
Qty.	20 pc(s).

Data sheet

W-Series WAP WDK2.5/4 N

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	1.5 mm	Height	60 mm
Depth	53.9 mm	Net weight	4.185 g

Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C
----------------------------------	--------	----------------------------------	--------

Additional technical data

Installation advice	Direct mounting	Version	End plate
---------------------	-----------------	---------	-----------

Material data

Material	Wemid	Colour	Dark Beige
UL 94 flammability rating	V-0		

System specifications

Product family	W-Series	Mounting rail	none
----------------	----------	---------------	------

Classifications

ETIM 3.0	EC000886	ETIM 4.0	EC000886
ETIM 5.0	EC000886	ETIM 6.0	EC000886
UNSPSC	30-21-18-27	eClass 5.1	27-14-11-33
eClass 6.2	27-14-11-33	eClass 7.1	27-14-11-33
eClass 8.1	27141133	eClass 9.0	27141133

Approvals

ROHS	Conform
------	---------

Downloads

STEP	1084000000_31494_WAP_WDK2.5-4_N_STP.stp
------	---