


# Accessories

## Ferrules with plastic collars



	Nominal-cross section (mm <sup>2</sup> )	AWG	Dimensions (mm)				Stripping-length		Qty.
			L 1	L 2	D 1	D 2	mm		
0.14	0.14	26	10	6	0.6	1.5	8	500	
	0.14	26	12	8	0.6	1.5	10	500	
0.25	0.25	24	10	6	0.8	1.8	8	500	
	0.25	24	12	8	0.8	1.8	10	500	
0.34	0.34	22	10	6	0.8	2	8	500	
	0.34	22	12	8	0.8	2	10	500	
0.5	0.5	20	10	6	1	2.6	8	500	
	0.5	20	12	6	1	2.6	8	500	
	0.5	20	14	8	1	2.6	10	500	
	0.5	20	14	8	1	2.6	10	5000	
0.75	0.75	20	16	10	1	2.6	12	500	
	0.75	18	12	6	1.2	2.8	8	500	
	0.75	18	14	8	1.2	2.8	10	500	
	0.75	18	14	8	1.2	2.8	10	5000	
1	0.75	18	16	10	1.2	2.8	12	500	
	0.75	18	18	12	1.2	2.8	14	500	
	1	17	12	6	1.4	3	8	500	
	1	17	14	8	1.4	3	10	500	
1.5	1	17	14	8	1.4	3	11	5000	
	1	17	16	10	1.4	3	12	500	
	1	17	18	12	1.4	3	15	500	
	1.5	16	14	8	1.7	3.5	10	500	
2.5	1.5	16	14	8	1.7	3.2	10	5000	
	1.5	16	14	8	1.7	3.2	10	500	
	1.5	16	16	10	1.7	3.5	12	500	
	1.5	16	18	12	1.7	3.5	15	500	
	1.5	16	24	18	1.7	3.5	20	500	
	2.5	14	14	8	2.2	4.2	10	500	
4	2.5	14	14	8	2.2	4	11	3000	
	2.5	14	14	8	2.2	4	11	500	
	2.5	14	18	12	2.2	4.2	14	500	
	2.5	14	24	18	2.2	4.2	20	500	
6	4	12	17	10	2.8	4.8	12	500	
	4	12	20	12	2.8	4.8	14	500	
	4	12	26	18	2.8	4.8	20	500	
10	6	10	20	12	3.5	6.3	14	100	
	6	10	26	18	3.5	6.3	20	100	
16	10	7	22	12	4.5	7.6	15	100	
	10	7	28	18	4.5	7.6	21	100	
25	16	6	24	12	5.8	8.8	15	100	
	16	6	28	18	5.8	8.8	21	100	
35	25	3	30	16	7.3	11.2	18	50	
	25	3	36	22	7.3	11.2	24	50	
	35	2	30	16	8.3	12.7	19	50	
50 ...	35	2	30	18	8.3	12.7	21	50	
	35	2	39	25	8.3	12.7	28	50	
	50	1	36	20	10.3	15	26	50	
	50	1	40	25	10.3	15	31	50	
	70	2/0	37	20	12.7	16	26	25	
95	3/0	44	25	14.7	18	31	25		
120	4/0	50	30	16.5	21	36	25		
150	300 MCM	54	32	18.5	23.5	38	25		

## Weidmüller standard


Type	Colour	Cat. No.	Strip pack Cat. No.	Ferrules in strip form Cat. No.	Ferrules on reels Cat. No.
H 0.14/10	grey		9005180000		
H 0.14/12	grey		9028240000		
H 0.25/10	light blue	9025740000	9026050000		
H 0.25/12	light blue	9025760000	9025780000		
H 0.34/10	torquoise	9025750000	9026030000		
H 0.34/12	torquoise	9025770000	9025790000		
H 0.34/12	torquoise				9004390000
H 0.5/10	orange		9028260000		
H 0.5/12	orange	0409500000			
H 0.5/14	orange	0690700000	9026060000	9004270000	
H 0.5/14	orange				9005810000
H 0.5/16	orange	9025870000	9028270000		
H 0.75/12	white	0409600000	9028280000		
H 0.75/14	white	0462900000	9026070000	9004290000	
H 0.75/14	white				9005820000
H 0.75/16	white	9025860000	9028290000		
H 0.75/18	white	9025910000	9028300000		
H 1/12	yellow	0409700000	9028310000		
H 1/14	yellow	0463000000	9026080000	9004320000	
H 1/14	yellow				9005830000
H 1/16	yellow	9025950000	9028320000		
H 1/18	yellow	9025930000	9028340000		
H 1.5/14	red	0463100000	9026090000		
H 1.5/14	red				9005840000
H 1.5/14	red			9004340000	
H 1.5/16	red	0635100000	9028350000		
H 1.5/24	red	0565600000			
H 2.5/14 D	blue	9019160000	9026100000		
H 2.5/14 D	blue				9005850000
H 2.5/14 D	blue			9004360000	
H 2.5/18 D	blue	9019170000			
H 2.5/24 D	blue	9019180000			
H 4/17 D	grey	9019190000	9026010000*		
H 4/20 D	grey	9019200000			
H 4/26 D	grey	9019210000			
H 6/20	black	0533500000			
H 6/26	black	0565700000			
H 10/22	ivory	0534200000			
H 10/28	ivory	0565800000			
H 16/24	green	0565900000			
H 16/28	green	0566000000			
H 25/30	brown	0317000000			
H 25/36	brown	0317100000			
H 35/30	beige	0317200000			
H 35/39	beige	0317300000			
H 50/36	oliv	0444200000			
H 70/40	yellow	9028200000			
H 95/44	red	9028210000			
H 120/50	blue	9028220000			
H 150/54	yellow	9028230000			

Strip pack 5 x 100 ferrules  
\* 5 x 50 ferrules



## Accessories

### Twin ferrules with plastic collars




	Nominal-cross section (mm <sup>2</sup> )	AWG	Dimensions (mm)			Stripping-length		mm	Qty.
			L 1	L 2	D 1	A/B			
0.5	0.5	20	15	8	1.4	5/3	11	500	
	0.5	20	16	10	1.4	5/3	13	500	
	0.5	20	19	12	1.4	5/3	15	500	
0.75	0.75	18	15	8	1.7	5.5/3	11	500	
	0.75	18	17	10	1.7	5.5/3	13	500	
	0.75	18	24	18	1.7	5.5/3	21	500	
1	1.0	17	16	8	2.2	6.5/3.6	12	500	
	1.0	17	15	8	2.0	5.8/3.2	12	500	
	1.0	17	19	12	2.0	5.8/3.2	16	500	
	1.0	17	25	18	2.0	5.8/3.2	22	500	
1.5	1.5	16	16	8	2.2	6.5/3.6	11	500	
	1.5	16	20	12	2.2	6.5/3.6	15	500	
	1.5	16	26	18	2.2	6.5/3.6	21	500	
2.5	2.5	14	19	10	2.8	8/4.5	13	500	
	2.5	14	19	10	2.8	8/4.5	13	250	
	2.5	14	21	12	2.8	8/4.5	15	500	
	2.5	14	21	12	2.8	8/4.5	15	250	
	2.5	14	27	18	2.8	8/4.5	21	500	
4	4.0	12	22	12	3.5	9/5.2	15	100	
	4.0	12	28	18	3.5	9/5.2	21	100	
6	6.0	10	25	12	4.5	11.4/6.2	20	100	
	6.0	10	29	18	4.5	11.4/6.2	24	100	
10	10.0	7	24	12	5.8	13.4/7.6	17	100	
	10.0	7	30	18	5.8	13.4/7.6	23	100	
	10.0	7	24	12	6.5	13.4/7.6	17	100	
	10.0	7	30	18	6.5	13.4/7.6	23	100	
16	16.0	6	29	16	8.3	17.2/9.5	20	50	
	16.0	6	38	25	8.3	17.2/9.5	29	50	

### Weidmüller standard

Type	Colour	Cat. No.	Strip pack Cat. No.
H 0.5/15	orange	9037200000	9004440000*
H 0.5/16.5	orange	9037210000	
H 0.5/18.5	orange	9037220000	
H 0.75/15	white	9037230000	9018510000*
H 0.75/17	white	9037240000	9004900000*
H 0.75/24.5	white	9037250000	
H 1/15S	yellow	9018690000	9018650000*
H 1/15	yellow	9037260000	9018530000*
H 1/20	yellow	9037270000	9004910000*
H 1/25.6	yellow	9037280000	
H 1.5/16	red	9037290000	9004410000*
H 1.5/20	red	9037300000	9004920000*
H 1.5/25.6	red	9037310000	
H 2.5/18.5D	blue	9037500000	
H 2.5/18.5D	blue		9004430000**
H 2.5/20.5D	blue	9037510000	
H 2.5/20.5D	blue		9004740000**
H 2.5/26.5D	blue	9037520000	
H 4/22D	grey	9037530000	9004730000***
H 4/28D	grey	9037540000	
H 6/25	black	9037320000	9004930000***
H 6/29	black	9037330000	
H 10/26	ivory	9037340000	9004940000***
H 10/30	ivory	9037350000	
H 10/24 S	ivory	9018860000	
H 10/30 S	ivory	9018870000	
H 16/29	green	9037360000	
H 16/38	green	9037370000	

\* 5 x 100 \*\* 5 x 50 \*\*\* 5 x 20

### Ferrules for short-circuit-proof and earthing-proof conductors



	Nominal-cross section (mm <sup>2</sup> )		Dimensions (mm)				Stripping-length		mm	Qty.	Type	Colour	Strip pack Cat. No.
	mm <sup>2</sup>	AWG	L 1	L 2	D 1	D 2	mm	mm					
1.5	1.5	16	17.5	8	1.8	6.8	13	100		H 1.5/17.5XS	black	9006590000	
	1.5	16	19.5	10	1.8	6.8	15	100		H 1.5/19.5XS	black	9006630000	
2.5	2.5	14	17.5	8	2.3	7.6	14	100		H 2.5/17.5XS	blue	9006670000	
	2.5	14	21.5	12	2.3	7.6	17	100		H 2.5/21.5XS	blue	9006710000	
4	4	12	19.5	10	2.9	7.8	14	100		H 4/19.5XS	grey	9006750000	
6	6	10	23	12	3.6	8.1	17	100		H 6/23XS	yellow	9006790000	
10	10	7	24	12	4.6	9.6	17	100		H 10/24.5XS	red	9006830000	
16	16	6	25.5	12	6	11.9	26	100		H 16/25.5XS	blue	9006870000	

DIN


Type	Colour	Cat. No.	Strip pack Cat. No.
H 0.5/15D	● white	9037380000	9004780000*
H 0.5/16.5D	● white	9037390000	
H 0.5/18.4D	● white	9037400000	
H 0.75/15D	● grey	9037410000	9018520000*
H 0.75/17D	● grey	9037420000	9004770000*
H 0.75/24.5D	● grey	9037430000	
H 1/15D	● red	9037440000	9018540000*
H 1/20D	● red	9037450000	9004760000*
H 1/25.6D	● red	9037460000	
H 1.5/16D	● black	9037470000	9004420000*
H 1.5/20D	● black	9037480000	9004750000*
H 1.5/25.6D	● black	9037490000	
H 2.5/18.5D	● blue	9037500000	
H 2.5/18.5D	● blue		9004430000**
H 2.5/20.5D	● blue	9037510000	
H 2.5/20.5D	● blue		9004740000**
H 2.5/26.5D	● blue	9037520000	
H 4/22D	● grey	9037530000	9004730000***
H 4/28D	● grey	9037540000	
H 6/25D	● yellow	9037550000	9004720000***
H 6/29D	● yellow	9037560000	
H 10/26D	● red	9037570000	9004710000***
H 10/30D	● red	9037580000	
H 10/24 DS	● red	9018880000	
H 10/30 DS	● red	9018890000	
H 16/29D	● blue	9037590000	
H 16/38D	● blue	9037600000	

Others

Type	Colour	Cat. No.	Strip pack Cat. No.
H 0.5/15	● orange	9037200000	
H 0.5/16.5	● orange	9037210000	
H 0.5/18.5	● orange	9037220000	
H 0.75/15T	● light blue	9037610000	9018570000*
H 0.75/17T	● light blue	9037620000	9005140000*
H 0.75/24.5T	● light blue	9037630000	
H 1/15D	● red	9037440000	9018540000*
H 1/20D	● red	9037450000	9004760000*
H 1/25.6D	● red	9037460000	
H 1.5/16D	● black	9037470000	9004420000*
H 1.5/20D	● black	9037480000	9004750000*
H 1.5/25.6D	● black	9037490000	
H 2.5/18.5T	● grey	9037640000	
H 2.5/18.5T	● grey		9018580000**
H 2.5/20.5T	● grey	9037650000	
H 2.5/20.5T	● grey		9005150000**
H 2.5/26.5T	● grey	9037660000	
H 4/22T	● orange	9037670000	9018590000***
H 4/28T	● orange	9037680000	
H 6/25T	● green	9037690000	9005160000***
H 6/29T	● green	9037700000	
H 10/26T	● brown	9037710000	9005170000***
H 10/30T	● brown	9037720000	
H 16/29T	● white	9037730000	
H 16/38T	● white	9037740000	

\* 5 x 100 \*\* 5 x 50 \*\*\* 5 x 20

Ferrules with plastic collars special sizes




	Nominal-cross-section (mm <sup>2</sup> )	AWG	Dimensions (mm)				Stripping-length mm	Qty.	Type	Colour	Cat. No.	Strip pack Cat. No.
			L 1	L 2	D 1	D 2						
0.5	0.5	20	14	8	1	2.9	10	500	H 0.5/14 S	● orange	9004560000	
	0.5	20	14	8	1	2.9	10	500	H 0.5/14 DS	● white	9004590000	
0.75	0.75	18	14	8	1.2	3.4	10	500	H 0.75/14 S	● white	9025960000	9025700000*
	0.75	18	14	8	1.2	3.4	10	500	H 0.75/14 TS	● light blue	9018550000	
1	1	17	14	8	1.4	3.5	10	500	H 1/14 S	● yellow	9025970000	9025710000*
	1	17	14	8	1.4	3.5	10	500	H 1/14 DS	● red	9018560000	
1.5	1.5	16	12	6	1.7	3.5	8	500	H 1.5/12 S	● red	9025690000	
	1.5	16	14	8	1.7	3.9	10	500	H 1.5/14 S	● red	9025980000	9025720000*
	1.5	16	14	8	1.7	3.9	10	500	H 1.5/14 DS	● black	9025240000	9028360000*
2.5	2.5	14	12	6	2.2	4.2	8	500	H 2.5/12 DS	● blue	9028490000	
	2.5	14	14	8	2.2	4	10	500	H 2.5/14 DS	● blue	1333100000	
	2.5	14	16	10	2.2	4.2	13	500	H 2.5/16 DS	● blue	9036220000	
	2.5	12	12	6	2.2	4.2	8	500	H 2.5/12 TS	● grey	9036200000	
	2.5	14	14	8	2.2	4.2	10	500	H 2.5/14 TS	● grey	9426770000	
2.5	14	14	16	10	2.2	4.2	13	500	H 2.5/16 TS	● grey	9036210000	
4.0	4.0	12	14	8	2.8	4.8	10	500	H 4.0/14 DS	● grey	9028520000	
	4.0	12	15	8	2.8	4.8	12	500	H 4.0/15 TS	● orange	9036230000	

\* 5 x 100 ferrules


## Accessories

### Ferrules without plastic collars



		Nominal cross-section		Dimensions (mm)			Stripping-length		Type	Cat. No.
		(mm <sup>2</sup> )	AWG	L 1	D 1	D 2	mm	Qty.		
<b>0.25</b>		<b>0.25</b>	<b>24</b>	5	0.7	1.65	5	1000	<b>H 0.25/5</b>	<b>9018910000</b>
<b>0.5</b>		<b>0.5</b>	<b>20</b>	6	1	2.1	6	1000	<b>H 0.5/6</b>	<b>0282600000</b>
		<b>0.5</b>	<b>20</b>	10	1	2.1	10	1000	<b>H 0.5/10</b>	<b>9004050000</b>
<b>0.75</b>		<b>0.75</b>	<b>18</b>	6	1.2	2.3	6	1000	<b>H 0.75/6</b>	<b>0282700000</b>
		<b>0.75</b>	<b>18</b>	10	1.2	2.3	10	1000	<b>H 0.75/10</b>	<b>0542500000</b>
<b>1</b>		<b>1</b>	<b>17</b>	6	1.4	2.5	6	1000	<b>H 1/6</b>	<b>0372600000</b>
		<b>1</b>	<b>17</b>	10	1.4	2.5	10	1000	<b>H 1/10</b>	<b>0282800000</b>
<b>1.5</b>		<b>1.5</b>	<b>16</b>	7	1.7	2.8	7	1000	<b>H 1.5/7</b>	<b>0372700000</b>
		<b>1.5</b>	<b>16</b>	10	1.7	2.8	10	1000	<b>H 1.5/10</b>	<b>0186500000</b>
		<b>1.5</b>	<b>16</b>	12	1.7	2.8	12	1000	<b>H 1.5/12</b>	<b>9004060000</b>
		<b>1.5</b>	<b>16</b>	18	1.7	2.8	18	1000	<b>H 1.5/18</b>	<b>9004070000</b>
<b>2.5</b>		<b>2.5</b>	<b>14</b>	7	2.2	3.4	7	1000	<b>H 2.5/7</b>	<b>0373000000</b>
		<b>2.5</b>	<b>14</b>	10	2.2	3.4	10	1000	<b>H 2.5/10</b>	<b>9004080000</b>
		<b>2.5</b>	<b>14</b>	12	2.2	3.4	12	1000	<b>H 2.5/12</b>	<b>0186100000</b>
		<b>2.5</b>	<b>14</b>	18	2.2	3.4	18	1000	<b>H 2.5/18</b>	<b>9004090000</b>
<b>4</b>		<b>4</b>	<b>12</b>	9	2.8	4	9	500	<b>H 4/9</b>	<b>0373100000</b>
		<b>4</b>	<b>12</b>	12	2.8	4	12	1000	<b>H 4/12</b>	<b>0244100000</b>
		<b>4</b>	<b>12</b>	15	2.8	4	15	1000	<b>H 4/15</b>	<b>9004100000</b>
		<b>4</b>	<b>12</b>	18	2.8	4	18	1000	<b>H 4/18</b>	<b>9004110000</b>
<b>6</b>		<b>6</b>	<b>10</b>	10	3.5	4.7	10	500	<b>H 6/10</b>	<b>9004120000</b>
		<b>6</b>	<b>10</b>	12	3.5	4.7	12	500	<b>H 6/12</b>	<b>0191900000</b>
		<b>6</b>	<b>10</b>	15	3.5	4.7	15	500	<b>H 6/15</b>	<b>0124700000</b>
		<b>6</b>	<b>10</b>	18	3.5	4.7	18	500	<b>H 6/18</b>	<b>9004130000</b>
<b>10</b>		<b>10</b>	<b>7</b>	12	4.5	5.8	12	500	<b>H 10/12</b>	<b>0282900000</b>
		<b>10</b>	<b>7</b>	15	4.5	5.8	15	500	<b>H 10/15</b>	<b>0124800000</b>
		<b>10</b>	<b>7</b>	18	4.5	5.8	18	500	<b>H 10/18</b>	<b>0379300000</b>
<b>16</b>		<b>16</b>	<b>6</b>	12	5.8	7.5	12	500	<b>H 16/12</b>	<b>0492500000</b>
		<b>16</b>	<b>6</b>	15	5.8	7.5	15	500	<b>H 16/15</b>	<b>0124300000</b>
		<b>16</b>	<b>6</b>	18	5.8	7.5	18	100	<b>H 16/18</b>	<b>0375200000</b>
		<b>16</b>	<b>6</b>	25	5.8	7.5	25	100	<b>H 16/25</b>	<b>9004150000</b>
		<b>16</b>	<b>6</b>	32	5.8	7.5	32	100	<b>H 16/32</b>	<b>9004160000</b>
<b>25</b>		<b>25</b>	<b>3</b>	15	7.3	9.5	15	250	<b>H 25/15</b>	<b>0124400000</b>
		<b>25</b>	<b>3</b>	18	7.3	9.5	18	100	<b>H 25/18</b>	<b>0375300000</b>
		<b>25</b>	<b>3</b>	25	7.3	9.5	25	100	<b>H 25/25</b>	<b>9004170000</b>
		<b>25</b>	<b>3</b>	32	7.3	9.5	32	100	<b>H 25/32</b>	<b>9004180000</b>
<b>35</b>		<b>35</b>	<b>2</b>	18	8.3	11	18	100	<b>H 35/18</b>	<b>0368900000</b>
		<b>35</b>	<b>2</b>	25	8.3	11	25	100	<b>H 35/25</b>	<b>9004190000</b>
		<b>35</b>	<b>2</b>	30	8.3	11	30	500	<b>H 35/30 S</b>	<b>9451000000</b>
		<b>35</b>	<b>2</b>	32	8.3	11	32	100	<b>H 35/32</b>	<b>9004200000</b>
<b>50 ...</b>		<b>50</b>	<b>1</b>	18	10.3	13	18	100	<b>H 50/18</b>	<b>9004210000</b>
		<b>50</b>	<b>1</b>	25	10.3	13	25	100	<b>H 50/25</b>	<b>9025880000</b>
		<b>50</b>	<b>1</b>	32	10.3	13	32	100	<b>H 50/32</b>	<b>9004220000</b>
		<b>70</b>	<b>2/0</b>	25	12.5	15	25	50	<b>H 70/25</b>	<b>9004230000</b>
		<b>70</b>	<b>2/0</b>	32	12.5	15	32	50	<b>H 70/32</b>	<b>9004240000</b>
		<b>95</b>	<b>3/0</b>	25	14.5	17	25	50	<b>H 95/25</b>	<b>9004250000</b>
		<b>95</b>	<b>3/0</b>	32	14.5	17	32	50	<b>H 95/32</b>	<b>9004260000</b>
		<b>120</b>	<b>4/0</b>	32	16.5	19	32	50	<b>H 120/32</b>	<b>9036240000</b>
		<b>150</b>	<b>300 MCM</b>	32	18.5	21	32	50	<b>H 150/32</b>	<b>9036250000</b>
		<b>185</b>	<b>350 MCM</b>	32	20	23.5	32	50	<b>H 185/32</b>	<b>9036260000</b>

### Hook-shaped cable lugs in accordance with ESI 50-18 part 2



		Nominal-cross-section		Dimensions (mm)			Qty.	Type	Cat. No.
		(mm <sup>2</sup> )	AWG	L 1	L 2	B			
<b>0.25...1.5</b>	<b>24</b>	27.2	16.75	4.6		2	<b>HB 1-17</b>	<b>9036290000</b>	
<b>1.0...2.5</b>	<b>24</b>	27.2	16.75	3.0		2	<b>HB 1-13</b>	<b>9036300000</b>	