

TORQUE WRENCH 3/8 INCH DRIVE 110NM

Item ID: 3892AG-E3



- 3/8" drive torque wrench covering 20-110Nm
- Equipped with an in-built angular gauge for easier after tightening of stretch bolts (TTY torque to yield fasteners)
- Click type mechanism with easily recognisable signal when the required torque is reached
- Simple to adjust and easy to read Nm scale
- Additional ft/lb reference scale (range 15-75 ft/lb)
- Clearly marked with three bands to show the correct place on the handle where pressure should be applied to give a more accurate torque reading
- Twist locking facility to ensure the set torque is maintained
- Reversible 24 teeth ratchet mechanism (DIN3122) giving 15° increments for strength and for added reference when torquing stretch bolts
- Designed to torque right hand (clockwise) fasteners
- Accurate to +/- 4% and conforms to ISO6789 for assured reliability and accuracy
- Individually tested and certified at the time of manufacture
- Each torque wrench has it's own individual certification number for easier quality control management
- Supplied in a handy storage case

Length (mm): 330

Width (mm): 415

Height (mm): 285

Weight (kg): 1.25

Technical changes and errors may occur

WWW.TENGOOLS.COM



Get organised™