



DEWALT 12/18V XR 3 X 360 Green Cross Line Laser - Bare Unit

DCE089NG18-XJ



- Projects 3x 360° Self levelling lines (2x intersecting vertical and 1x horizontal or cross line)
- Green beam laser diode provides full brightness for visibility and extended working range
- Durable IP54 rating for protection against dust and water ingress from jobsites
- Variable blink sequence for manual mode
- Working range: 20m (50m with detector)
- Accuracy: +/-3mm@10m
- Full-time pulse mode allows use with detector maintains full brightness for visibility
- Fine adjustment knob to adjust vertical beam lines quickly and accurately for enhanced productivity and accuracy
- Locking Pendulum to help prevent damage to internal components
- Integrated ¼" and 5/8" thread for tripod attachment

Description:

The DEWALT 12/18V 3x 360° Cross Line Laser- Bare Unit projects bright horizontal or vertical highly accurate green beams with an accuracy of +/-3mm@10m. The unique fine adjust allows the user to quickly and accurately adjust the vertical beams for enhanced accuracy and productivity. Its durable design with IP54 rated water and debris resistance makes it ideal for jobsite applications. The green laser maintains full brightness for visibility, having a working range of 20m and detector range of 50m. The locking pendulum prevents damage of internal components during transportation. Ideal for room, electrical, stud wall, suspended ceiling and internal fixing layout as well as floor/wall tiling and point to point transfers. (Battery Not Included)

What we like - First cross line laser which is compatible with 18V & 12V XR batteries, features a green beam for enhanced visibility.

Supplied With:

- Laser Target
- Wall mount bracket
- TSTAK compatible Box

Specifications	
Laser type	3 x 360°
Voltage	18/ 12 V
Working range	30m
Beam colour	Green
Accuracy	+/-3mm@10m
Laser class	2
Tripod fitting	¼" 5/8" Thread