


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER E.O. P20271	27JUL2009	DM	RDR
	B	REVISED PER E.O. P21283	25JAN2012	DM	RDR
	C	REVISED PER PCN E-18-001206	24JAN2018	JA	DM
	C1	REVISED PER PCN E-19-008828	04JUN2019	JA	DM



TE INTERNAL PN	DEUTSCH PN	PLATING
0462-005-2031	0462-005-2031	GOLD
0462-005-20141	0462-005-20141	NICKEL
0462-005-20309	0462-005-20309	TIN

3. WIRE RANGE : 18 AWG TO 16 AWG [0.75 - 1.0 mm²]

2 SOCKET CONTACT IS IDENTIFIED BY A SINGE PURPLE STRIPE.

1. THIS CONTACT MAY BE CRIMPED WITH HDP-400 POWER PRESS OR HDT-48-00 HAND TOOL.

NOTES: UNLESS OTHERWISE SPECIFIED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. MEYER 14SEP2007		
DIMENSIONS: INCHES [mm]		CHK D. MEYER 23JAN2012		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. REED 03FEB2012	NAME CONTACT SOCKET SIZE 20	
0 PLC ±		PRODUCT SPEC 0425-015-0000	SIZE A3	
1 PLC ±		APPLICATION SPEC 0425-205-0000	CAGE CODE 4AFU8	DRAWING NO 0462-005-20XX
2 PLC ±		WEIGHT 0.26g	RESTRICTED TO -	
3 PLC ±		CUSTOMER DRAWING	SCALE 12:1	SHEET 1 OF 1
4 PLC ±			REV C1	
ANGLES ±				
FINISH				