




28MV

Insulated T-Handle Socket Wrenches



PRODUCT DETAILS



- Dip-coated insulation
- 3-layer safety colour code insulation
- For working on live equipment up to 1000 V according to IEC 60900
- 6-point dynamic-drive profile
- Opening tolerance according to ISO 691
- Made from high-performance alloy steel
- 3 Multi-layer coating with different colours indicating safety, danger or high danger. Plus a 4th one in black to further protect handle edges
- This provides protection as well as creating a visual warning system
- If the outer insulation layer gets damaged, the lighter colour underneath will become visible and warn the user
- Each and every tool is tested to 10.000V for 10 seconds at the end of the manufacturing cycle



Follow the Fish!



PRODUCT ATTRIBUTES

Product		L	A	B	
28MV-8	8.0 mm	200 mm	190 mm	16.5 mm	101 g
28MV-9	9.0 mm	200 mm	190 mm	18 mm	143 g
28MV-10	10.0 mm	200 mm	190 mm	19.5 mm	150 g
28MV-11	11.0 mm	200 mm	190 mm	20.5 mm	159 g
28MV-12	12.0 mm	200 mm	190 mm	22 mm	216 g
28MV-13	13.0 mm	200 mm	190 mm	23 mm	260 g
28MV-14	14.0 mm	200 mm	190 mm	24.5 mm	272 g
28MV-15	15.0 mm	200 mm	190 mm	25.5 mm	312 g
28MV-16	16.0 mm	200 mm	190 mm	27 mm	322 g
28MV-17	17.0 mm	200 mm	190 mm	28 mm	331 g
28MV-18	18.0 mm	200 mm	190 mm	29.5 mm	421 g
28MV-19	19.0 mm	200 mm	190 mm	30.5 mm	435 g
28MV-20	20.0 mm	200 mm	190 mm	32.5 mm	515 g
28MV-21	21.0 mm	200 mm	190 mm	33 mm	531 g
28MV-22	22.0 mm	200 mm	190 mm	34.5 mm	579 g

