




A002S

002 Jobber Drill - Pouch Pack

NEW
2014.01

TiN Tipped and Split Point



d ₁ Øh ₈ Inch	d ₁ Øh ₈ mm	d ₁ decimal Inch	l ₂ mm	l ₁ mm	e-code	
	2.00	0.0787	24	49	A002S2.0	
	2.50	0.0984	30	57	A002S2.5	
	3.00	0.1181	33	61	A002S3.0	
1/8	3.18	0.1252	36	65	A002S1/8	
	3.20	0.1260	36	65	A002S3.2	
	3.30	0.1299	36	65	A002S3.3	
	3.50	0.1378	39	70	A002S3.5	
5/32	3.97	0.1563	43	75	A002S5/32	
	4.00	0.1575	43	75	A002S4.0	
	4.10	0.1614	43	75	A002S4.1	
	4.20	0.1654	43	75	A002S4.2	
	4.50	0.1772	47	80	A002S4.5	
3/16	4.76	0.1874	52	86	A002S3/16	
	5.00	0.1969	52	86	A002S5.0	
13/64	5.16	0.2031	52	86	A002S13/64	
	5.50	0.2165	57	93	A002S5.5	
7/32	5.56	0.2189	57	93	A002S7/32	
	6.00	0.2362	57	93	A002S6.0	
1/4	6.35	0.2500	63	101	A002S1/4	
	6.50	0.2559	63	101	A002S6.5	
17/64	6.75	0.2657	69	109	A002S17/64	
	6.80	0.2677	69	109	A002S6.8	
	7.00	0.2756	69	109	A002S7.0	
	7.50	0.2953	69	109	A002S7.5	
5/16	7.94	0.3126	75	117	A002S5/16	
	8.00	0.3150	75	117	A002S8.0	
	8.20	0.3228	75	117	A002S8.2	
	8.50	0.3346	75	117	A002S8.5	
	9.00	0.3543	81	125	A002S9.0	
	9.50	0.3740	81	125	A002S9.5	
3/8	9.52	0.3748	87	133	A002S3/8	
	10.00	0.3937	87	133	A002S10.0	

d ₁ Øh ₈ Inch	d ₁ Øh ₈ mm	d ₁ decimal Inch	l ₂ mm	l ₁ mm	e-code	
	10.20	0.4016	87	133	A002S10.2	
	10.50	0.4134	87	133	A002S10.5	
	11.00	0.4331	94	142	A002S11.0	
	11.50	0.4528	94	142	A002S11.5	
	12.00	0.4724	101	151	A002S12.0	
	12.50	0.4921	101	151	A002S12.5	
1/2	12.70	0.5000	101	151	A002S1/2	
	13.00	0.5118	101	151	A002S13.0	