

Terminal blocks 32 A



Image representative of range

Specifications

Current Rating	57A
Material	PP
Maximum Operating Temperature	+100°C
Minimum Operating Temperature	-25°C
Number of Ways	12
Termination Method	Screw Down
Voltage Rating	380 V
Wire Size	10 mm