

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200850015](#)  
**Status:** **Active**  
**Overview:** Brad Ultra-Lock Connection System  
**Description:** Ultra-Lock (M12) Single Keyway with PG7 Cable Fitting, Female, 4 Pole, 90° Angle, Cable Diameter 3.30-6.60mm

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Field Attachable / Accessories
Series	<a href="#">120085</a>
Approvals	N/A
IP Rating	IP69K
Material - Contact	Brass
Overview	<a href="#">Brad Ultra-Lock Connection System</a>
Product Name	Ultra-Lock (M12)
Taxonomy	Circular Industrial Connectors
Type	Field Attachable Connector
UPC	78678897656

**Physical**

Cable Diameter	3.30-6.60mm (.130-.260")
Coupling Type	Push to Lock
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	Single
Material - Connector Body	PA
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	20.140/g
Orientation	90° Angle
Poles	4
Temperature Range - Operating	-25°C to +90°C
Wire Size AWG	18

**Electrical**

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC / 300V DC

**Material Info**

Engineering Number	WA4001-31
--------------------	-----------

**Reference - Drawing Numbers**

Sales Drawing	SD-120085-006-001
---------------	-------------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT\_CE -

Declaration of

Conformity

ZZCERT\_UKCA

- Declaration of

Conformity

**China RoHS**

50 Image

Not Relevant

Not Contained

CER\_4000408919\_00\_000.pdf

CER\_4000410298\_00\_000.pdf

**Search Parts in this Series**

[120085 Series](#)