



[Home](#) / [LEDs](#) / [Surface Mount LEDs](#) / [Surface Mount LEDs - CMDA1 Series](#) / [LED SMT 2.0V 20mA Yellow](#)



LED SMT 2.0V 20mA Yellow

SKU: CMDA1CY7A1X

Category: [Surface Mount LEDs - CMDA1 Series](#)

Description

Stock Availability

Technical Downloads

Product Description

CMDA1 Series is a SMD LED with high intensity light output. Available in multiple single color options and a 70 degree viewing angle.

Additional Information

Led Package Color

Clear

Led Style

Rectangle with Flat Top

LED Mounting Method

SMD

LED Size

1206

Lens Type

Non-Diffused Lens

LED output Color

Yellow

Luminous Intensity Typ. (mcd)

6 mcd

Peak Wavelength (nm) *580 nm*

LED Voltage Forward Max. (V) *2.5 V*

LED Voltage Forward Min. (V) *–*

LED Voltage Forward Typ. (V) *2.2 V*

LED Forward Current Max. (mA) *70 mA*

Viewing Angle *70 degree viewing angle*

RoHS *Yes*

REACH Compliant *Yes*

Conflict Mineral Free *Yes*

LED Feature *–*

Luminous Intensity Min. (mcd) *3 mcd*

Luminous Intensity Max. (mcd) *–*