

PART NAME	NON-METALLIC ENCLOSURE (STYLE B)	PART No.	NBB-10245 & NBB-10265 & NBB-15245 & NBB-22245
-----------	----------------------------------	----------	---

MATERIAL:
UL LISTED INDOOR VERSION
 SOLID BODY & COVER _____ ABS/PC BLENDED PLASTIC
 UL94-5VB FLAMMABILITY RATING
 CLEAR COVER _____ POLYCARBONATE PLASTIC
 UL94V-0 FLAMMABILITY RATING
 UV STABILIZED
UL LISTED OUTDOOR VERSION
 SOLID BODY & COVER _____ PBT/PC BLENDED PLASTIC
 UL94-5VA FLAMMABILITY RATING
 UV STABILIZED
ABS VERSION
 SOLID BODY & COVER _____ ABS
 UL94-HB FLAMMABILITY RATING

FINISH:
 BODY _____ LIGHT GRAY
 COVER _____ LIGHT GRAY OR CLEAR
 LATCHES & HINGES _____ NON-METALLIC
 WALL MOUNTING BRACKETS _____ STAINLESS STEEL


INDUSTRY STANDARDS:
UL LISTED INDOOR VERSION
 UL508 TYPE 1, 2, 3, 3R, 4, 4X INDOOR, 12 & 13
 NEMA TYPE 1, 2, 3, 3R, 4, 4X, 12 & 13
 IEC529-IP65
UL LISTED OUTDOOR VERSION
 UL508 TYPE 1, 2, 3, 3R, 4, 4X, 12 & 13
 NEMA TYPE 1, 2, 3, 3R, 4, 4X, 12 & 13
 IEC529-IP65
ABS VERSION
 NEMA TYPE 1, 2, 3, 3R, 4, 4X, 12 & 13
 IEC529-IP65

ALL VERSIONS
 GASKET _____ MODIFIED POLYURETHANE

NOTE: UNIT COMES COMPLETE WITH
 (4) WALL MOUNTING BRKTS.
 & (4) M5 x 10mm LG. TRUSS
 HD. MACHINE SCREWS (NOT
 SHOWN)

COVER INCLUDES GRAY POLY-
 URETHANE GASKET.

INTERNAL HINGED PANEL MOUNTING
 BRACKETS, AIR & MOISTURE VENTS,
 STAINLESS STEEL LOCKING HASP
 AND GALVANIZED STEEL INTERNAL
 PANEL ARE NOT INCLUDED, BUT
 CAN BE PURCHASED SEPARATELY.



0.575 [15] DIA. BOSS WITH 0.166 [4] DIA.
 HOLE x 0.395 [10] DEEP (4) PLACES
 BOSSES ACCEPT M5 METRIC OR #10 STD. SHEET
 METAL SCREWS x 0.375 [9] LG. (NOT SUPPLIED)

0.575 [15] DIA. BOSS WITH
 M5 x 0.8mm THREADED BRASS
 INSERT - (4) PLACES INSIDE
 (4) PLACES OUTSIDE

DIMENSIONS = INCHES
 [MILLIMETERS]

NOTE: ALL DIMENSIONS HAVE ±0.039 [±1] TOLERANCE
 UNLESS OTHERWISE SPECIFIED

VIEW LESS COVER				DIMENSIONS													
UL LISTED INDOOR VERSION	UL LISTED OUTDOOR VERSION	ABS VERSION		A	B	C	D	E	F	G	H	J	K	L	M	N	P
PART NO.	PART NO.	PART NO.															
SOLID COVER	CLEAR COVER	SOLID COVER	SOLID COVER														
NBB-10245	NBB-10265	NBB-15245	NBB-22245	13.010	12.144	11.013	9.846	13.000	12.140	11.020	9.846	5.857	1.185	12.435	12.225	12.425	12.215
				[330]	[308]	[280]	[250]	[330]	[308]	[280]	[250]	[149]	[30]	[316]	[311]	[316]	[310]